



Product: <u>9815</u> 2

 100Ω Twinax, #20-1c TC/1c BC, PO, Duofoil® + 2 TC Braids, PE Jkt, Direct Burial

Product Description

100 Ohm Twinax, 20 AWG stranded (7x28) .037" one tinned/ one bare copper conductors, polyethylene insulation, Duofoil® + tinned copper braid shield (95% coverage), high-density polyethylene jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor					
AWG	Stranding	Material	Construction n x D	No. of C	onductors
20	7x28	TC - Tinned Copper	Stranded	1	
20	7x28	BC - Bare Copper	Stranded	1	
Condu	Conductor Count:				2

Insulation

Material	Nominal Wall Thickness
PE - Polyethylene	0.024 in

Color Chart

Number	Color
1	Natural & Natural

Inner Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PE - Polyethylene	0.236 in	0.035 in

Outer Shield

Туре	Layer	Material	Material Trade Name	Coverage [%]
Таре	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Tinned Copper (TC)		95%
Table	Notes:		Polyethylene	

Outer Jacket

Mat	aterial	Nominal Diameter	Nominal Wall Thickness
PE - Pol	olyethylene	0.33 in	0.034 in
Table No	Notes:		

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
9.5 Ohm/1000ft	2 Ohm/1000ft	2 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield	Nom. Capacitance Conductor to Shield
14.5 pF/ft	23 pF/ft	14.5 pF/ft

Inductance

Nominal Inductance

0.155 µH/ft

Impedance

Nominal Characteristic Impedance 100 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.4 dB/100ft
10 MHz	1.1 dB/100ft
50 MHz	2.5 dB/100ft
100 MHz	4.1 dB/100ft
200 MHz	6.4 dB/100ft
400 MHz	10.2 dB/100ft

Delay

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
66 ns/100m	1.54 ns/ft	66%

High Frequency

Frequency [MHz]
1 MHz
10 MHz
50 MHz
100 MHz
200 MHz
400 MHz

Voltage

Non-UL Voltage Rating					
600 V RMS					
Electrical Characteristics Notes:	Capacitance conductor to shield: 23.0 pF/ft				
Temperature Range					

Operating Temperature Range:	-55°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	62 lbs/1000ft
Max. Pull Tension:	115 lbs
Min. Bend Radius/Minor Axis:	3.5 in

Standards

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes	
Plenum/Non-Plenum		
Plenum (Y/N):	Νο	

Variants Color Put-Up Type Length UPC Item # 9815 010500 Black Reel 500 ft 612825259053 9815 0101000 Black Reel 1.000 ft 612825259039 Footnote: C - CRATE REEL PUT-UP. **Product Notes** Notes: Polyethylene flooding grease applied over outer shield. History

Update and Revision:

Revision Number: 0.344 Revision Date: 05-05-2023

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.