

Vibration Monitoring and Machine Protection Systems

1010 East Main Street, League City, TX 77573 Phone:281.334.0766 Fax: 281.334.4255 www.stiweb.com / www.stiwebstore.com

CMCP603H Series **High Temperature 3 Socket MS Cable Assembly IP68 Locking Collar Connector - Yellow FEP Jacket - IP68**





Features:

- High Temperature Cable Assembly
- Rugged Design for Permanent Installations
- 3 Socket MS Connector, MIL-C 5015 Style
- IP68 Locking Collar (Screw On)
- Viton Boot for Superior Chemical Resistance
- Yellow FEP Jacketed Cable
- UV, Oil and Chemical Resistant
- Suitable for Class 1 Division 1/2 Locations
- Braided Shield with Drain Wire
- 200°C Temperature Rating
- Lifetime Warranty

Typical Applications

Mates with Sensors Featuring a 3 Pin MS Connector

Connector Specifications

Connector Type: 3 Socket (Female) MS 5015 MIL-C 5015 Style

Shield Isolation: Case Isolated 316 Stainless Steel Locking Collar Material:

IP Rating IP68

Cable Specifications

Jacket Material: FEP (Fluorinated Ethylene Propylene)

Jacket Color: Yellow Fiberglass Insulation:

3 Plus Drain Wire Conductors:

Wire AWG: 20AWG (0.52mm^2) 24AWG (0.21mm^2) Drain Wire AWG: Shieldina: Braided Shield

Cable Diameter: 0.20" (5.08mm)0.048 Lbs/Ft (1.48kg/m)Weight: Temperature Range: -67 to +392°F $(-55 \text{ to } +200^{\circ}\text{C})$ Capacitance Per Foot (pF/ft): 26pF/ft (85.3pF/m)

Optional Armor Specifications

316 Stainless Steel Material: Type: Hose or Braided Armor Diameter Hose = 0.29''(7.37mm)Braid = 0.23" (5.84mm)



Cable Shown with Stainless Steel Hose Armor and Push On Connector




Cable Shown with Stainless Steel Braided Armor and Locking Collar Connector

Connector Pinout / Wire Color

Color Code: A = White

B = Back

C = Red



Ordering Information:

| Ordering Information. | | | | | |
|-----------------------|----------|-----|-----|-------|---|
| СМСР603Н | -XX | -XX | -XX | -XX | 3 Socket MS Cable Assembly, Locking Collar Connector |
| | -16 | | | | 16' (5m) Long |
| | -32 | | | | 32' (10m) Long |
| | -64 | | | | 64' (20m) Long |
| | -Specify | | | | Specify Cable Length in Feet |
| | | -01 | | | Standard Cable, No Armor |
| | | -02 | | | Cable with Overall Stainless Steel Hose Armor |
| | | -03 | | | Cable with Overall Stainless Steel Braided Armor |
| | | | -01 | | Tinned Leads on Fly End (Terminal Block Connection) |
| | | | -02 | | Spade Lugs Installed on Leads (Screw Terminal Connection) |
| | | | | BLANK | Isoalted - Shield Not Connected at Sensor End (Standard) |
| | | | | -NI | Non-Isolated – Shield Connected at Sensor End |
| | | | | | |

Example Part Number:

CMCP603H-16-01-01 3 Socket MS Cable Assembly 16' (5m) Long Standard Cable, No Armor Tinned Leads on Fly End

Similar Products:



CMCP602HST Push On IP68 Connector



CMCP602H IP68 Locking Collar