



Product: <u>1502SB</u> ☑

Media Control, 1 Pair 22 AWG TC, 2 Cond. 18 AWG, LSZH Jacket, CMG-LS

Product Description

Multimedia Control Cable, 1 Pair 22 AWG stranded (7x30) tinned copper (data) with FEP insulation, Beldfoil® shield w/ drain, 2 Conductor 18 AWG stranded (16x30) tinned copper conductor (power) with Flamarrest® insulation, CMG-LS, LSZH jacket

Technical Specifications

Product Overview

Suitable Applications: Multi-Media & Lighting AutoMultimedia Control Cable, Rated-CMG-LS, 2-22 AWG stranded tinned copper pairs (data) with Datalene® insulation, Beldfoil® shield, drain, 1-18 AWG stranded tinned copper pair with polypropylene insulation, unshielded, LSZH jacketmation / Control, ABS Type Approved

Construction Details

Conductor

Element	Size	Stranding	Material
22 AWG	22	7x30	TC - Tinned Copper
18 AWG	18	16x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code	Notes
18 AWG	PE - Polyethylene (Foam)	0.007 in (0.18 mm)	0.061 in (1.5 mm)	Blue & White, Red & Black	HDPE
22 AWG	PP - Polypropylene	0.020 in (0.51 mm)	0.0685 in (1.74 mm)		

Inner Shield

Shield Type	Material	Coverage
Таре	Bi-Laminate (Alum+Poly)	100%

Outer Shield



Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.045 in (1.1 mm)	0.255 in (6.48 mm)	Yes

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Max. Current
16.3 Ohm/1000ft	14 pF/ft (46 pF/m)	38 pF/ft (120 pF/m)	100 Ohm	3.8 Amps per Conductor at 25°C
6.9 Ohm/1000ft (23 Ohm/km)				

Voltage



Mechanical Characteristics

75°C	-30°C To +75°C
Max. Pull Tension:	59.8 lbs (2
Bulk Cable Weight	: 39 lbs/100

Standards and Compliance

UL Temperature Operating

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Non-Halogenated, Sunlight Resistance	
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, Limited Smoke, IEC 60332-1-2, IEC 60332-3-22	
CPR Compliance:	CPR Euroclass: Dca-s1,d1,a1	
NEC / UL Compliance:	Article 800, CMG-LS	
CEC / C(UL) Compliance:	CMG-ST1	
IEEE Compliance:	Std. 45 clause 23	
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)	
UK Regulation Compliance:	UKCA Mark	
APAC Compliance:	China RoHS II (GB/T 26572-2011)	
Other Standard Compliance(s):	UL444, ABWS Type Approval Certificate 06-HS184641C	

History

Jpdate and Revision:	Revision Number: 0.483 Revision Date: 05-03-2023		
----------------------	--	--	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
1502SB 0101000	Black	Reel	1,000 ft	612825116028

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.