SIEMENS

Data sheet 6XV1870-3RH10

product type designation

product description



IE TP XP Cord RJ45/RJ45, 4x2

Crossover patch cable, preferred length, preassembled with two RJ45 connectors (10/100/1000/10000MB)

Industrial Ethernet TP XP Cord RJ45/RJ45, CAT 6A, crossed TP cable 4x2, pre-assembled with 2 RJ45 plugs, length 1 m.

suitability for use	Easy connection of terminal devices to the IE FC cabling system	
cable designation	LI 02YSCH 4x2x0,15 PIMF GN FRNC	
wire length	1 m	
electrical data		
number of electrical connections	2	
attenuation factor per length		
• at 10 MHz / maximum	0.086 dB/m	
• at 100 MHz / maximum	0.28 dB/m	
at 300 MHz / maximum	0.501 dB/m	
• at 600 MHz / maximum	0.735 dB/m	
impedance		
at 1 MHz 100 MHz	100 Ω	
• at 10 MHz 600 MHz	100 Ω	
relative symmetrical tolerance		
 of the characteristic impedance at 1 MHz 100 MHz 	15 %	
 of the characteristic impedance at 10 MHz 600 MHz 	10 %	
transfer impedance per length / at 10 MHz	10 mΩ/m	
loop resistance per length / maximum	290 mΩ/m	
operating voltage		
 RMS value 	80 V	
NVP value in percent	80 %	
mechanical data		
number of electrical cores	8	
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin- plated copper wires	
core diameter		
 of AWG26 insulated conductor 	0.5 mm	
outer diameter		
 of inner conductor 	0.5 mm	
 of the wire insulation 	1 mm	
 of cable sheath 	6.2 mm	
symmetrical tolerance of the outer diameter / of cable sheath	0.3 mm	
material		
 of the wire insulation 	polyethylene (PE)	

of cable sheath	FRNC
color	
 of the insulation of data wires 	white/blue, white/orange, white/green, white/brown
 of cable sheath 	green
bending radius	
with single bend / minimum permissible	31 mm
 with multiple bends / minimum permissible 	43.5 mm
weight per length	50 kg/km
ambient conditions	
ambient temperature	
during operation	-25 +80 °C
during storage	-25 +80 °C
during transport	-25 +80 °C
during installation	-25 +80 °C
• note	In fixed installation -40 °C to 80 °C
fire behavior	flame resistant according to IEC 60332-1-2, smoke density according to IEC 61034
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil	oil resistant according to IEC 60811-2-1 (4 h / 70°C)
• to grease	Conditional resistance
radiological resistance / to UV radiation	not resistant
protection class IP	IP20
product features, product functions, product components	/ general
product feature	
• halogen-free	Yes
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	Yes; E130266 AWM STYLE 21279
certificate of suitability	
EAC approval	Yes
UL approval	Yes
RoHS conformity	Yes
standard for structured cabling	Cat6A
Marine classification association	
American Bureau of Shipping Europe Ltd. (ABS)	No
French marine classification society (BV)	No
Det Norske Veritas (DNV)	No
Germanische Lloyd (GL)	No
Lloyds Register of Shipping (LRS)	No
Nippon Kaiji Kyokai (NK)	No
Polski Rejestr Statkow (PRS)	No
reference code	
• according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
further information / internet-Links	
Internet-Link	
to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
to website: Information and Download Center	http://www.siemens.com/industry/infocenter
 to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
 to website: CAx-Download-Manager 	http://www.siemens.com/cax
to website: Industry Online Support	https://support.industry.siemens.com
last modified:	6/25/2022 🖸