

6	5	4	3	2	1
ITEM	PART#	DESCRIPTION	QTY	UOM	
A,B	16020082	SL Fem Crimp Term 24-30 15Gold Reel x	2	PC	



PART NUMBER	TITLE	CABLE DESCRIPTION	LENGTH 'L'	CABLE COLOR
2196801221	SL F-F 75mm 24 awg lead BK Au	1X24AWG DISC MPPE BK UL11028 HKUP	75±3	BLACK
2196801222	SL F-F 150mm 24 awg lead BK Au	1X24AWG DISC MPPE BK UL11028 HKUP	150±4	BLACK
2196801223	SL F-F 225mm 24 awg lead BK Au	1X24AWG DISC MPPE BK UL11028 HKUP	225±4	BLACK
2196801224	SL F-F 300mm 24 awg lead BK Au	1X24AWG DISC MPPE BK UL11028 HKUP	300±4	BLACK
2196801225	SL F-F 450mm 24 awg lead BK Au	1X24AWG DISC MPPE BK UL11028 HKUP	450±4	BLACK
2196802221	SL F-F 75mm 24 awg lead RD Au	1X24AWG DISC MPPE RD UL11028 HKUP	75±3	RED
2196802222	SL F-F 150mm 24 awg lead RD Au	1X24AWG DISC MPPE RD UL11028 HKUP	150±4	RED
2196802223	SL F-F 225mm 24 awg lead RD Au	1X24AWG DISC MPPE RD UL11028 HKUP	225±4	RED
2196802224	SL F-F 300mm 24 awg lead RD Au	1X24AWG DISC MPPE RD UL11028 HKUP	300±4	RED
2196802225	SL F-F 450mm 24 awg lead RD Au	1X24AWG DISC MPPE RD UL11028 HKUP	450±4	RED

NOTES:

1. Crimping to be done as per Molex standards.
2. The product specification relies on the terminals & wire spec.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2022/03/03	A	INITIAL RELEASE	SAIKIG
DOCUMENT STATUS	P1	RELEASE DATE	2022/03/18 07:25:12

FUNCTIONAL SYMBOLS FA = 0 FE = 0 FP = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		
	DIMENSION UNITS	SCALE	GENERAL TOLERANCES (UNLESS SPECIFIED)		
DIVISIONAL SYMBOLS	mm	NTS	ANGULAR TOL ± °		
	4 PLACES	±	EC NO: 698265		PRODUCT CUSTOMER DRAWING
	3 PLACES	±	DRWN: SAIKIG 2022/03/03		
	2 PLACES	±	CHK'D: MNARAYAN01 2022/03/18		DOCUMENT NUMBER: 2196801221 DOC TYPE: PSD DOC PART: 000 REVISION: A
	1 PLACE	±	APPR: MNARAYAN01 2022/03/18		
	0 PLACES	±	INITIAL REVISION:		MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET SHEET NUMBER: 1 OF 1
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING: A4-SIZE	
			SERIES: 219680		