



**Product:** <u>9776</u> ♂

Audio, Control & Instrument, #18-12pr, PO, Indiv. Foil, PVC Jkt, CM

# **Product Description**

Audio, Control & Instrument Cable, 18 AWG stranded (19x30) tinned copper conductors, polypropylene insulation, 12 twisted pairs, individually shielded with Beldfoil® (100% coverage), 20 AWG stranded tinned copper drain wire, PVC jacket.

# **Technical Specifications**

## **Product Overview**

Suitable Applications:	Low Voltage Analog Signals (4-20ma, 0-10v,); Low Voltage Digital Control (24v,); Line Level Audio; Computer Communication; Panel Wiring

## **Construction Details**

#### Conductor

	Element	Number of Element	Size	Stranding	Material
ľ	Pair(s)	12	18 AWG	19x30	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Color Code
Pair(s)	l	0.019 in (0.48 mm)	Black & Red, Black & White, Black & Green, Black & Blue, Black & Yellow, Black & Brown, Black & Orange, Red & White, Red & Green, Red & Blue, Red & Yellow, Red & Brown

## Inner Shield

Element Shield Type		Material	Coverage	Drainwire Type	Notes
Pair(s)	Таре	Bi-Laminate (Alum+Poly)	100%	20 AWG (7x28) TC	each pair

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloric	le 0.052 in (1.3 mm	0.735 in (18.7 mm)
Overall Cable Diamete	r (Nominal):	.735 in (18.7 mm)

# **Electrical Characteristics**

## Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Pair(s)	6.4 Ohm/1000ft (21 Ohm/km)	30 pF/ft (98 pF/m)	55 pF/ft (180 pF/m)	50 Ohm	66%	2.7 Amps per Conductor at 25°C

#### Voltage

UL Voltage Rating
300 V (CM), 30 V (UL AWM 2929)

# **Mechanical Characteristics**

## Temperature

UL Temperature	Operating	
80°C (UL AWM 2919)	-20°C to +80°C	

#### Bend Radius

Stationary Min.	Installation Min.
7.4 in (190 mm)	7.4 in (190 mm)

Max. Pull Tension:	744 lbs (337 kg)
Bulk Cable Weight:	275 lbs/1000ft (409 kg/km)

#### **Standards and Compliance**

Environmental Suitability:	Indoor	
Flammability / Reaction to Fire: UL1685 UL Loading		
NEC / UL Compliance:	Article 800, CM	
AWM Compliance:	AWM 2919	
CEC / C(UL) Compliance: CM		
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)	
APAC Compliance:	China RoHS II (GB/T 26572-2011)	

## **History**

Update	and Revision:	Revision Number: 0.428 Revision Date: 05-05-2023

#### **Part Numbers**

#### Variants

Item #	Color	Putup Type	Length	UPC
9776 060100	Chrome	Reel	100 ft	612825258582
9776 060500	Chrome	Reel	500 ft	612825258605
9776 0601000	Chrome	Reel	1,000 ft	612825258599

#### © 2023 Belden, Inc

#### All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.