



**Product:** 9533 ☑

RS-232, #24-3c, SR-PVC, O/A Foil, PVC Jkt, CMG

# **Product Description**

Computer EIA RS-232 Cable, 24 AWG stranded (7x32) tinned copper conductors, PVC insulation, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

# **Technical Specifications**

### **Product Overview**

Suitable Applications: RS-232 Applications; Computer Communications; Low Voltage Analog Signals (4-20mA, 0-10V, ...); Low Voltage Digital Control (24V, ...); Line Level Audio; Panel Wiring

## **Construction Details**

### Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	3	24 AWG	7x32	TC - Tinned Copper

#### Insulation

Elem	ent	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conduc	ctor(s)	SR-PVC - Polyvinyl Chloride (Semi-Rigid)	0.011 in (0.28 mm)	0.044 in (1.1 mm)	Black, White, Red

#### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

### **Outer Jacket**

	Material	Nom. Thickness	Nom. Diameter
	PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.162 in (4.11 mm)
ľ	Overall Cable Diameter (N	Nominal): 0.162 in (	4.11 mm)

#### **Electrical Characteristics**

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	25 Ohm/1000ft	33 pF/ft (110 pF/m)	65 pF/ft (210 pF/m)	2.2 Amps per Conductor at 25°C

### Voltage

UL Voltage Rating
300 V (CMG), 300 V (UL AWM 2464)

## **Mechanical Characteristics**

### Temperature

UL Temperature	Operating
60°C (UL CMG);80°C (UL AWM 2464)	-30°C to +80°C

#### Bend Radius

Stationary Min.	Installation Min.
1.9 in (48 mm)	1.9 in (48 mm)

Max. Pull Tension:	22 lbs (10.0 kg)
Bulk Cable Weight:	15 lbs/1000ft

### **Standards and Compliance**

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

### History

Update and Revision:	Revision Number: 0.529 Revision Date: 03-04-2023	

#### **Part Numbers**

#### **Variants**

Item #	Color	Putup Type	Length	UPC/EAN
9533.0030	Chrome	Reel	30 m	8719605021687
9533 060100	Chrome	Reel	100 ft	612825255048
9533.00U152	Chrome	UnReel	152 m	8719605021694
9533.01152	Chrome	Reel	152 m	8719605021717
9533.00U305	Chrome	UnReel	305 m	8719605021700
9533.01305	Chrome	Reel	305 m	8719605021724
9533 060500	Chrome	Reel	500 ft	612825255062
9533 060U500	Chrome	UnReel	500 ft	612825255031
9533 0601000	Chrome	Reel	1,000 ft	612825255055
9533 060U1000	Chrome	UnReel	1,000 ft	612825255024
9533 0605000	Chrome	Reel	5,000 ft	612825255079

## © 2023 Belden, Inc

#### All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.