



Notes:

1. Electrical:
 - Meets EIA/TIA-568-B.2-10 Cat.6A Channel Specification
 - Connector Operating Temperature: -40°C to +85°C
2. Materials and Finish:
 - Coupling Ring: Polyester (Black) or Metallized ABS (Nickel Plated); UL94 V-0
 - Plug Housing: Polyester (Black) or Metallized ABS (Nickel Plated); UL94 V-0
 - Interfacial Seal: Silicon, Color: White
 - Cable Gland: PA (Black) or Brass, Nickel Plated
 - Cable Gland Seal: NBR, Color: Black
 - Cable Gland Insert (Metal Version): Nylon, Color: White
 - Cat.6A RJ45 Plug Metal Shell: Copper Alloy, Nickel Plated
 - Cat.6A RJ45 Plug Plastic Housing: Clear Polycarbonate UL94 V-2
 - Cat.6A RJ45 Plug Contacts: Phosphor Bronze, Finish: 50u" Gold min. over Nickel
 - Cable: Cat.6A SSTP, 4 Pairs, AWG26, Stranded, Jacket Color: Black

Directive 2002/95/EC RoHS Compliant

Cable Length L	Plastic Version	Metallized Plastic Version
2 m	17-150544	17-150574
4 m	17-150554	17-150584
5 m	17-150564	17-150594
15 m	17-151004	17-151014

Note: Special cable length are available please contact factory

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF CONEC CORPORATION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified			Scale: NTS	Dim. in meter
	Name	Title	Approval Date	0 PLC ±0.50	1 PLC ±0.38		Material: See Notes Cat.6A RJ45 Ethernet Patch Cords IP67 Industrial to Strain Relief	Drawing No.: 17k1A275 Part No.: SEE PART NUMBER TABLE
				2 PLC ±0.25	3 PLC ±0.10			
				ANGLES ±3°				
	2011 Date Name Draw. Sept. 28 Vincent Ke Appd. Sept. 28 J. Chaudry Norm D-old							
Rev	Changes	Date	Name					