



8	—
7	—
6	RX-
5	—
4	—
3	RX+
2	TX-
1	TX+
PIN	说明



PCBLAYOUT TOP VIEW
TOL:±0.05

NOTES:

- HOUSING MATERIAL:GLASS FILLED POLYESTER UL94V-0.
 - CONTACT MATERIAL:PHOSPHOR BRONZE.
 - PLATING: GOLD PLATED ON CONTACT AREA, 100u"MIN. TIN PLATED ON SOLDERING AREA, 50u"MIN. NICKEL PLATED OVERALL.
 - SHELL:BRASS,T=0.20. WITH 40u" NICKEL PLATED.
 - LED:T=0.50, TIN PLATED.
- ELECTRICAL:
- VOLTAGE RATING: 125V AC RMS.
 - CURRENT RAIING: 1.5AMP.
 - CONTACT RESISTANCE: 30MILLIOHMS MAX.
 - INSULATION RESISTANCE: 500MEGOHMS MIN @500V DC.
- MECHANICAL:
- DURRABILITY: 750 CYCLES MIN.
 - INSERTION FORCE : 22N MAX.
 - REMOVAL FORCE(WITHOUT PLUG LOCK) : 22N MAX.
- ENVIRONMENTAL:
- STORAGE: -40°C~85°C
 - OPERATION: -40°C~85°C
 - REFLOW SOLDERING Temperature,255±5°C.
- *Apply to the EU standards(ROSH)
1. ① ~ ⑫ FOR QIP DIM.



LED Specification

Standard LED Color	LED Wavelength	Foward	Foward
Green	565nm	20mA	1.8-2.4V
Yellow	585nm	20mA	1.8-2.4V
ORANGE	585nm	20mA	1.8-2.8V

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: RJ45 沉板4.2 SMT有壳有灯LCP黑
			PAR RJ45-004-045-11
DECIMALS:	ANGLES:		DWN
.X:±0.35	X':±3'		CHKD
.XX:±0.25	.X':±2'	APVD	
.XXX:±0.15	.XX':±1'	CUSTOMER COPY	SCALE:1:1 UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A