










NOTES:

1. HOUSING MATERIAL:LCP UL94V-0.
  2. CONTACT MATERIAL:COPPER ALLOY,T=0.30.
  3. PLATING: GOLD PLATED ON CONTACT AREA, 100u"MIN. TIN PLATED ON SOLDERING AREA, 50u"MIN. NICKEL PLATED OVERALL.
  4. SHELL:COPPER ALLOY,T=0.20. 40u"MIN. NICKEL PLATED OVERALL.
- ELECTRICAL:
1. VOLTAGE RATING: 125V AC RMS.
  2. CURRENT RAIING: 1.5AMP.
  3. CONTACT RESISTANCE: 40MILLIOHMS MAX.
  4. INSULATION RESISTANCE: 500MEGOHMS MIN @100V DC.
- MECHANICAL:
1. DURRABILITY: 750 CYCLES MIN.
  - 2.INSERTION FORCE : 22N MAX.
  - 3.REMOVAL FORCE(WITHOUT PLUG LOCK) : 22N MAX.
- ENVIRONMENTAL:
1. STORAGE: -40°C~85°C
  2. OPERATION:-40°C~85°C
- \*Apply to the EU standards(ROSH)
1.  $\varnothing 1 \sim \varnothing 6$  FOR QIP DIM.



PCBLAYOUT TOP VIEW  
TOL:±0.05(THICKNESS=1.60)



MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: RJ45 壳版1.8有壳DIP
			PAR RJ45-001-002-11
DECIMALS:	ANGLES:		DWN
X.X±0.35	X.*±3°		CHKD
X.XX=0.25	X.X*±2°	APVD	SCALE:1:1
X.XXX=0.10	X.XX*±1°	CUSTOMER COPY	UNIT:MM
		SIZE:A4	REV:A