


# molex

**INSULATION DISPLACEMENT CABLE:**  
0.050" PITCH, 28 AWG, 19/40 STRANDED, EXTRUDED FEP



Cond. No.	Part Number	Span	Width
2	1000570226	1.3 ± 0.051mm (0.050" ± 0.002")	2.54 ± 0.13mm (0.100" ± 0.005")

CHARACTERISTICS		
<b>Conductor</b>	28 AWG, 19/40, Silver Plated Copper	
<b>Insulation</b>	FEP	
<b>Color</b>	Natural	
<b>Impedance (ohms)</b>	115 Unbalanced	165 Balanced
<b>Capacitance (pF/ft)</b>	10.5 Unbalanced	6.0 Balanced
<b>Inductance (uH/ft)</b>	0.14 Unbalanced	0.16 Balanced
<b>Insulation Resistance (Mohm)</b>	>500	
<b>Voltage Rating</b>	300V	
<b>Temperature Rating</b>	200C	

**STANDARD PACKAGING**

100 ft./spool, 10 Ft. minimum length

**UL STYLE 20424**