# **Detailed Specifications & Technical Data**





73804WS Multi-Conductor - 600V Shielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles



For more Information please call

1-800-Belden1

## **General Description:**

18 AWG stranded (16x30) bare copper conductors, PVC insulation, oil-resistant PVC inner jacket, tinned copper braid shield, 85% coverage, oil-resistant overall PVC jacket.

4

## **Physical Characteristics (Overall)**

#### Conductor

#### AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (mm)
3	18	16x30	BC - Bare Copper	1.194

**Total Number of Conductors:** 

#### Gr

ound Wire		
Ground Wire (Y/N):	Υ	
Ground Wire AWG:	18	
Ground Wire Stranding:	16X30	
Ground Wire Conductor Material:	BC - Bare Copper	
Ground Wire Insulation Material:	PVC - Polyvinyl Chloride	

#### Insulation

#### **Insulation Material:**

Insulation Material	Wall Thickness (mm) Dia. (mm	
PVC - Polyvinyl Chloride	0.559	2.311

#### **Insulation Color Code Chart:**

Color	Description	
Black	Individually Numbered	
Yellow/Green	Ground	

#### **Inner Jacket**

## Inner Jacket Material:

Inner Jacket Material	Nom Wall (mm)	Nom. Dia. (mm)
PVC - Polyvinyl Chloride	0.762	7.264

#### **Outer Shield**

#### **Outer Shield Material:**

Outer Shield Material	Coverage (%)
TC - Tinned Copper	85.000

**Outer Shield Separator Material:** Tissue Tape, 25% Overlap, Min.

## **Outer Jacket**

#### **Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.889

## **Overall Cable**

**Overall Nominal Diameter:** 9.754 mm

Me	Mechanical Characteristics (Overall)				
	Storage Temperature Range:	-40°C To +90°C			
	Installation Temperature Range:	Flexing: -5°C To +90°C			
	Operating Temperature Range:	Flexing: -5°C To +90°C			
	Bulk Cable Weight:	273.829 Kg/Km			

## **Detailed Specifications & Technical Data**





## 73804WS Multi-Conductor - 600V Shielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles

Max. Recommended Pulling Tension:	262.444 N
Min. Bend Radius/Minor Axis:	48.768 mm
Min. Bend/Installation:	48.768 mm
Min. Bend Radius (Continuous Flexing):	48.768 mm
Flex Cycle Rating:	1 Million Flexes

## **Applicable Specifications and Agency Compliance (Overall)**

### **Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	THHN/THWN Singles	
AWM Specification:	UL Style 2587 (600 V 90°C)	
CSA Specification:	600 V AWM I/II A/B	
EU Directive 2011/65/EU (ROHS II):	Yes	
Other Specification:	AWM/STYLE 2587, AWM I/II A/B, FT1, VDE 0472, Section 803 Oil Test, EU Low Voltage Directive 2014/35/EC, EU Directive 2011/65/EU(RoHS2), REACH Regulation (EC 1907/2006), California Proposition 65	
ame Test		
CSA Flame Test:	FT1	

## **Electrical Characteristics (Overall)**

#### Nom. Inductance:

Inductance (µH/m) 0.623

#### Nom. Capacitance Cond. to Other Cond. & Ground:

Description	Freq. (kHz) Capacitance (pl	
Nom. Cond. to Cond	1.000	144.364
Nom. Ground.	1.000	259.199

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km) 21.655

## Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km) 7.415

## **Put Ups and Colors:**

No put ups and colors are available for this product

Revision Number: 0 Revision Date: 09-27-2017

© 2020 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Page 2 of 2 10-11-2020