



APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/28/21	
A		ADDED SPEC.	5/24/21	LH/RC
B		ADDED PAGE 2	7/9/21	LH/RC
C		ADDED LENGTH 18MM	6/15/23	LH/NL
D		UPDATE SPEC.	8/8/23	LH/RC

Part Number	Size (mm)	As supplied (mm)		After recovered (mm)		Length
		I.D (D)	W.T (W)	I.D (max)	W.T (min)	
				(d)	(w)	
HST-00-BK-X	0.8	1.0±0.2	0.15±0.05	0.6	0.25	See Order Information
HST-01-BK-X	1.0	1.5±0.3	0.20±0.05	0.7	0.33	
HST-02-BK-X	1.5	1.5±0.3	0.20±0.05	0.8	0.34	
HST-03-BK-X	2.0	2.5±0.3	0.20±0.05	1.1	0.34	
HST-04-BK-X	2.5	3.0±0.3	0.25±0.05	1.25	0.42	
HST-05-BK-X	3.0	3.5±0.3	0.25±0.05	1.5	0.42	
HST-06-BK-X	3.5	4.0±0.3	0.25±0.05	1.75	0.42	
HST-07-BK-X	4.0	4.5±0.3	0.25±0.05	2.0	0.42	
HST-08-BK-X	4.5	5.0±0.3	0.25±0.05	2.25	0.42	
HST-09-BK-X	5.0	5.5±0.3	0.28±0.05	2.5	0.52	
HST-10-BK-X	6.0	6.5±0.3	0.28±0.05	3.0	0.52	
HST-11-BK-X	7.0	7.6±0.3	0.30±0.07	3.5	0.56	
HST-12-BK-X	8.0	8.6±0.3	0.30±0.07	4.0	0.56	
HST-13-BK-X	9.0	9.6±0.3	0.30±0.07	4.5	0.56	
HST-14-BK-X	10.0	10.7±0.4	0.30±0.07	5.0	0.56	
HST-15-BK-X	11.0	11.7±0.4	0.30±0.07	5.5	0.56	
HST-16-BK-X	12.0	12.7±0.4	0.30±0.07	6.0	0.56	
HST-17-BK-X	13.0	13.7±0.4	0.35±0.08	6.5	0.69	
HST-18-BK-X	14.0	14.7±0.4	0.35±0.08	7.0	0.69	
HST-19-BK-X	15.0	15.7±0.5	0.35±0.08	7.5	0.69	
HST-20-BK-X	16.0	16.7±0.5	0.35±0.08	8.0	0.69	
HST-21-BK-X	17.0	17.7±0.5	0.35±0.08	8.5	0.69	
HST-22-BK-X	18.0	19.0±0.5	0.40±0.10	9.0	0.77	
HST-23-BK-X	20.0	21.0±0.5	0.40±0.10	10.0	0.77	
HST-24-BK-X	22.0	23.0±0.5	0.40±0.10	11.0	0.77	
HST-25-BK-X	25.0	26.0±1.0	0.45±0.10	12.5	0.87	
HST-26-BK-X	28.0	29.0±1.0	0.45±0.10	14.0	0.87	
HST-27-BK-X	30.0	31.5±1.0	0.45±0.10	15.0	0.87	
HST-28-BK-X	35.0	36.5±1.0	0.50±0.10	17.5	0.97	
HST-29-BK-X	40.0	42.0±1.5	0.50±0.10	20.0	0.97	
HST-30-BK-X	45.0	47.0±1.5	0.50±0.10	22.5	0.97	
HST-31-BK-X	50.0	53.0±2.0	0.55±0.10	25.0	0.97	
HST-32-BK-X	60.0	63.0±3.0	0.60±0.15	30.0	1.17	
HST-33-BK-X	70.0	71.0±3.0	0.60±0.15	35.0	1.17	
HST-34-BK-X	80.0	81.0±3.0	0.65±0.15	40.0	1.20	
HST-35-BK-X	90.0	91.0±3.0	0.75±0.15	45.0	1.30	
HST-36-BK-X	100	101.0±3.0	0.75±0.15	50.0	1.30	
HST-37-BK-X	120	121.0±4.0	0.80±0.20	60.0	1.40	
HST-38-BK-X	150	151.0±4.0	0.80±0.20	75.0	1.50	
HST-39-BK-X	180	181.0±4.0	0.80±0.20	90.0	1.60	



BEFORE SHRINKING AFTER SHRINKING

HST-00-BK-X (0.8 SIZE only Black)

HST-XX-XX-X

TYPE SEE CHART

Color	Length
BK=Black	1= 1FT(12"inch)
WT=White	2= 2FT(24"inch)
RD=Red	3= 3FT(36"inch)
BU=Blue	4= 4FT(48"inch)
YW=Yellow	A= 18mm
GN=Green	
BN=Brown	
OR=Orange	
VT=Violet	
GY=Gray	
CL=Clear	

SPECIFICATIONS:
 Material: Polyolefin
 Electrical:
 Shrinkage: 2:1
 UL Style: UL224, 105°C VW-1 600V
 Temperature Rating:
 Operating temperature: -55°C to +125°C
 Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED



909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

DRAWN	LH	1/28/21
CHECKED	RC	1/28/21
APPROVED		

TITLE HEAT SHRINK TUBING, SINGLE WALL, FLAME RETARDANT POLYOLEFIN

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

SIZE X	PART NO. HST-XX-XX-X	REV. D
--------	----------------------	--------

REF: - SCALE: NTS SHEET 1 OF 2

6

5

4

3

2


1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
		RELEASED		

CARTON



PO:XXXXXXXX (SOXXXXXXXX) ADAM TECH P/N: HST-XX-XX-4 QTY: XXXX PCS LOT DTAE: XXXX POLYOLEFIN HEAT SHRINK TUBING		
--	--	--

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

DRAWN	LH	1/28/21
CHECKED	RC	1/28/21
APPROVED		

ADAM TECH
 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

TITLE	HEAT SHRINK TUBING, SINGLE WALL, FLAME RETARDANT POLYOLEFIN	
SIZE	PART NO.	REV.
X	HST-XX-XX-X	D
REF:	-	SCALE: NTS SHEET 2 OF 2

6

5

4

3

2

1