



Product: <u>89842</u> ☑

RS485, 2 Pr #24 Str TC, FEP Ins, OS+TC Brd, FEP Jkt, CMP

Product Description

RS-485, 2 Pair 24AWG (7x32) Tinned Copper, FEP Insulation, Overall Beldfoil®+Tinned Copper Braid(90%) Shield, FEP Outer Jacket, CMP

Technical Specifications

Product Overview

Suitable Applications: RS-485, POS; Computer communications; Low Voltage Analog Signals (4-20ma, 0-10v, ...); Low Voltage Digital Control (24v, ...); Line Level Audio; Panel Wiring; serial communication (RS-485 standard) comprising of PLCs, VFDs, HMIs, motors, RTU, SCADA, etc. within noisy environments over long distance, etc.

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	2	24 AWG	7x32	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	FEP - Fluorinated Ethylene Propylene (Foam)	0.023 in (0.58 mm)	0.070 in (1.8 mm)	White/Blue Stripe & Blue/White Stripe, White/Orange Stripe & Orange/White Stripe

Outer Shield

Shield Type	Shield Type Material		Drainwire Type
Таре	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC
Braid	Tinned Copper (TC)	90%	

Outer Jacket

Material		Nom. Thickness	Nom. Diameter
FEP - Fluorinated Ethyler	ne Propylene	0.020 in (0.51 mm)	0.345 in (8.76 mm)
Overall Cable Diameter (Nominal):	0.345 in (8.7	76 mm)	

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Pair(s)	24 Ohm/1000ft	12 pF/ft (39 pF/m)	22 pF/ft	120 Ohm	76%	4 Amps per Conductor at 25°C
Nom. Ou	Nom. Outer Shield DCR: 3.1 Ohm/1000ft (10 Ohm/km)					

High Frequency (Nominal/Typical)

Element	Frequency [MHz]	Nom. Insertion Loss (Attenuation)		
Pair(s)	1	0.6 dB/100ft		

Voltage

UL Voltage Rating 300 V (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating
200°C	-70°C to +200°C

Bend Radius

Standards and Compliance

Environmental Suitability:	Environmental Suitability: Indoor, Oil Resistance				
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6, IEC 60332-1-2				
CPR Compliance:	CPR Euroclass: Eca				
NEC / UL Compliance:	Article 800, CMP				
CEC / C(UL) Compliance:	CMP				
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)				
UK Regulation Compliance:	UKCA Mark				
APAC Compliance:	China RoHS II (GB/T 26572-2011)				
Non-Plenum Number:	9842				

Product Notes

Notes:	Oil and Gas Resistant	
. 10100.	of and odd freeholder.	

History

Update and Revision:	Revision Number: 0.532 Revision Date: 01-20-2023

Part Numbers

Variants

Item #	Color	UPC
89842 0021000	Red	612825221333
89842 002500	Red	612825221340

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.