深圳市凯越翔电子有限公司



陶振规格书

陶振
ZTT/24. 000 MHZ
0. 1%~0. 3%
KZT24000
董宗全

客户确认印栏		
认 证 印 章	负责人印章	
年 月 日	年 月 日	

拟制 成望生	审核	董宗全	核准	谢为亮
--------	----	-----	----	-----

本规格章程连同本页合共 6 页

工厂地址: 深圳市龙华区观澜人民路蔡发工业城一栋四层 TEL: 0755-89315823 89315866 FAX: 0755-89315223 官网: www.kaiyuexiang.com

1. SCOPE

(范围)

This specification is applied to the ceramics resonator used for microcomputer (本规格书适用于微电子用陶瓷谐振器)


2. MODEL NAME

(产品名称)

Part No. (产品号)	Customer's Part No.(顾客产品号)	Drawing No.(图号)
ZTT MX		XT-067

3. DIMENSIONS

(尺寸)



4. ELECTRICAL CHARACTERISTICS


(电气性能)

	Item	Requirements
	(项目)	(要求)
1	Oscillation Frequency(Fosc) (振荡频率)	24.000 MHZ
2	Frequency Tolerance (频率公差)	Fosc $\pm 0.1 \% \sim \pm 0.3\%$ (max)
3	Resonator Impedance (谐振阻抗)	30 Ω (max)
4	Build in Capacitor (内置电容)	30 pF±20% (max)
5	Operating Temp. Range (工作温度范围)	-20°C∼+70°C
3//	Temperature Stability	±0.5% (MAX)
6	(温度稳定性)	(-35℃~+85℃)
7	Max Voltage (最大电压)	6V DC; 15V P-P
8	Withstanding Voltage (耐电压)	D.C. 100V, 5Sec
9	Insulation Resistance (绝缘阻抗)	100M Ω min (D.C. 100V)
10	Aging(10 years) (10 年老化率)	±0.3 %
11	Storage Temp. Range (贮存温度范围)	-40°C~+85°C
12	Test Temp.&Humi.Condition (测试温、湿度条件)	+10°C~+30°C、40%~80%

5. TEST CIRCUIT

(测试电路)

Unless any necessity to measure under a standard condition(Temp: $20 \pm 2 \,^{\circ}$ C.Humi.: $65 \pm 5\%$)is occurred.(必要时标准测量条件为温度 $20 \pm 2 \,^{\circ}$ C,相对湿度 $65 \pm 5\%$)



IC: 1/6CD4069UBE×2

6. PHYSICAL AND ENVIRONMENTAL CHARACTERISTICS

(物理及环境特性)

	Test Item	Condition of Test	Requirements
	(试验项目)	(试验条件)	(要求)
1	Lead Strength (引脚强度) Lead Pulling (引脚拉力) Lead Bending	Force of 0.5kg is applied to each lead in axial direction for 10sec (沿每个引脚轴向施加 0.5kg 力保持 10 秒钟) When force of 0.25kg is applied to each lead in axial direction.the lead shall folded up to 90° from the axial direction and folded back to the axial direction.	No mechanical damage and the measured values shall meet Table 1.(无机械损伤,
	(引脚弯曲)	(沿引脚轴向施加 0.25kg 力的时候把引脚折弯 90 度后再折回原形)	测量值满足表 1 要求)
2	Solderability (可焊性)	Lead terminals are immersed in resin for 5 seconds and then immersing in a soldering bath(235±5℃)for 5±0.5sec.(引脚在助剂内浸 5 秒后再浸入 235±5℃ 的锡炉内 5±0.5 秒)	The solder shall coat at least 90% of the surface of terminal(引脚上锡覆盖率≥90%
	Storage in High	After being placed in a chamber with 85°C for 100	× .
3	Temp. (高温贮存)	hours and then being placed in natural condition for 1 hours, then measure.(85℃环境下存放 100 小时后取出自然存放 1 小时测试)	
4	Storage in Low Temp. (低温贮存)	After being placed in a chamber with -25℃ for 100 hours and then being placed in natural condition for 1 hours, then measure.(-25℃环境下存放 100 小时后取出自然存放 1 小时测试)	4
5	Humidity (潮湿)	After being placed in a chamber (Humi.:90~95%RH,Temp.:40±2℃) for 100 hours and then being placed in natural condition for 1 hours, then measure. (温度 40±2℃;湿度 90~95%的环境下存放 100 小时后取出自然存放 1 小时测试)	The measured value shall meet Table 1(测量值满
6	Thermal Shock (热冲击)	After temperature cycling of -55 ℃(30 minutes)to +85 ℃(30 minutes)was performed 5 times,Resonator shall be measured after being placed in natural condition for 1 hour(-55 ℃下 30 分钟到+85 ℃下 30 分钟循环 5 次后自然存放 1 小时测量)	足表 1 要求)
7	Resistance to soldering Heat (耐焊接热)	Lead terminals are immersed up to 2.0 mm from the root of terminals in solder bath of 265±5℃ for 10 ±1seconds, Resonator shall be measured after being placed in natural condition for 1 hour.(引脚距根部 2mm 以下浸入 265±5℃的锡炉中 10±1 秒取出自 然存放 1 小时测量)	

续	上表:			
8	Random	Resonator shall be measured after 3 times random dropping from the		
	Drop	hight of 1 m to concrete floor.(谐振器从1米高向水泥地板自由跌落3		
	(自由跌落)	次后测量)		
9		Resonator shall be measured after being applied vibration as below:(谐振器做如下振动后测量)		
	Vibration	Vibration Freq.(振动频率): 10 Hz to 55 Hz		
	(振动)	Amplitude(幅度): 1.5mm		
		Directions(方向): 3 axial directions (三轴向)		
		Time(时间): 1 hour/each direction(1 小时/向)		
10		The piezoelectric oscillator shall be subjected to 10 continuous		
		cycles,each as shown in figure below. Then the piezoelectric oscillator		
		shall be stored at standard atmospheric conditions for 24 h for		
		recovery,after which measurement shall be made.	The	
	- 140	• Temperature shall be reduced from 25 °C to -10 °C within 30 min.	measured	
		• Humidity uncontrolled at a temperature less than 25°C	value shall	
	74	用下图表示连续10次温湿度测试情况,然后在常温下放置24小时测	meet	
	Composite	试。在 30 分钟内将温度从 25℃ 调节至 -10℃,在温度低于 25℃时	Table 1(测	
	temperature	湿度无控制。	量值满足	
	/	75	表 1 要求)	
	Humidity	1		
	cycle test	70 90-96%RH 96%RH 90-96%RH 90-96%RH 90-96%RH		
	(温湿度测	60		
	试)			
		数 45 40 見 35		
		20 15		
		Voltage applied 5 Voltage applied		
		0 加电压		
		0 1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24		
	Time in hours 时间 (h)			

Table 1(表 1)

Item	Limit Value
(项目)	(限定值)
Oscillation Frequency(Fosc) (振荡频率)	≤±0.3%
Resonator Impedance (谐振阻抗)	≤±10Ω

Note: The limits in the above table are referenced to the initial measurements.(上表中的限定值参照初始测量值)

7. NOTICE

(注意)

- 1. Do not use this product with bend. The component may be damaged if excess Mechanical stress is applied to it mounted on the printed circuit board. (本产品不能折弯使用,在电路板安装时使用过大的机械压力可能造成产品损坏。)
- 2. This specification limits the quality of the component as a single Unit Please make sure that the component is evaluated and confirmed the drawing When it is mounted to your product. (本规格书只规定了部件本身的品质,应用于您的产品时请确认图纸该产品是否适用。)

8. Cutaway view

(剖面图)

