


## ■ 概述

L7912系列为3端负稳压电路,TO-220封装,有不同的固定输出电压,应用范围广。

## ■ 外形图及引脚排列




## ■ 主要特点

- 输出电流可达 1.5A, 输出电压有: -5V
- 过热保护
- 短路保护
- 输出晶体管SA补偿。

## ■ 极限值 ( $T_a=25^{\circ}\text{C}$ )

$V_I$ —	— 输入电压 .....	-3.5V
$T_{OPR}$ —	— 工作结温范围.....	0~125 $^{\circ}\text{C}$
$T_{STG}$ —	— 贮存温度范围.....	-65~150 $^{\circ}\text{C}$

## ■ 功能框图



(参见测试电路, 除非另有说明,  $0^{\circ}\text{C} \leq T_J \leq 125^{\circ}\text{C}$ ,  $I_o=500\text{mA}$ ,  $V_i=18\text{V}$ ,  $C_i=2.2\mu\text{F}$ ,  $C_o=1\mu\text{F}$ )

参数符号	符号说明	最小值	典型值	最大值	单位	测试条件
$V_o$	输出电压	-11.5	-12	-12.5	V	$T_J=25^{\circ}\text{C}$
		-11.4	-12	-12.6		$I_o=5.0\text{mA to } 1.0\text{A}$ , $P_o \leq 15\text{W}$ , $V_i=-15.5\text{V to } -27\text{V}$
$\Delta V_o$	电压调整率*		12	240	mV	$T_J=25^{\circ}\text{C}$ , $V_i=-14.5\text{V to } -30\text{V}$
			6	120		$T_J=25^{\circ}\text{C}$ , $V_i=-16\text{V to } -22\text{V}$
$\Delta V_o$	负载调整率*		12	240	mV	$T_J=25^{\circ}\text{C}$ , $I_o=5.0\text{mA to } 1.5\text{A}$
			4	120		$T_J=25^{\circ}\text{C}$ , $I_o=250\text{mA to } 750\text{mA}$
$I_q$	静态电流		3	6	mA	$T_J=25^{\circ}\text{C}$
$\Delta I_q$	静态电流变化率		0.05	0.5	mA	$I_o=5\text{mA to } 1.0\text{A}$
			0.1	1.0		$V_i=-15\text{V to } -30\text{V}$
$\Delta V_o/\Delta T$	输出电压温度系数		-0.8		mV/ $^{\circ}\text{C}$	$I_o=5\text{mA}$
$V_N$	输出噪声电压		200		$\mu\text{V}$	$T_A=25^{\circ}\text{C}$ , $f=10\text{Hz to } 100\text{kHz}$
RR	纹波抑制比	54	60		dB	$f=120\text{Hz}$ , $\Delta V_i=10\text{V}$
$V_D$	下降电压		2		V	$T_J=25^{\circ}\text{C}$ , $I_o=1\text{A}$
$I_{SC}$	短路电流		300		mA	$T_J=25^{\circ}\text{C}$ , $V_i=-35\text{V}$
$I_{PK}$	峰值电流		2.2		A	$T_J=25^{\circ}\text{C}$

■ 典型特性曲线

图1 输出电压




图2 负载调节




图3 静态电流




图4 下降电压





图5 短路电流



**NOTE:**

1. Exceeding the maximum ratings of the device in performance may cause damage to the device, even the permanent failure, which may affect the dependability of the machine. Please do not exceed the absolute maximum ratings of the device when circuit designing.
2. When installing the heat sink, please pay attention to the torsional moment and the smoothness of the heat sink.
3. MOSFETs is the device which is sensitive to the static electricity, it is necessary to protect the device from being damaged by the static electricity when using it.
4. Shenzhen Minos reserves the right to make changes in this specification sheet and is subject to change without prior notice.

**CONTACT:**

**深圳市迈诺斯科技有限公司（总部）**

地址：深圳市福田区华富街道田面社区深南中路4026号田面城市大厦22B-22C

邮编：518025

电话：0755-83273777