



1. 额定值 RATING: 8A 125/250VAC (UL, C-UL)  
12A-8(3)A 250V~ μ T125/55 (ENEC-17, CQC, CB)
2. 功能 FUNCTIONAL: 见电路图 SEE CIRCUIT DESCRIPTION
3. 接触电阻 CONTACT RESISTANCE: <50mΩ
4. 绝缘电阻 INSULATION RESISTANCE: >100MΩ (500VDC BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH: >1500VAC 0.5mA 1 MINUTE
6. 所有部件均使用环保材料  
ALL MATERIALS USE IN CONFORMIY WITH THE RoHS DIRECTIVE



CIRCUIT DIAGRAM



PANEL CUTOUT

无螺母

|    |             |    |             |                        |           |  |         |        |            |                   |     |             |      |
|----|-------------|----|-------------|------------------------|-----------|--|---------|--------|------------|-------------------|-----|-------------|------|
| 5  | →           | 10 | →           | DIMENSIONAL TOLERANCES |           | APPROVED                               | CHECKED | DESIGN | DRAWN      | ALL SIZE ARE IN   | MM  |             |      |
| 4  | →           | 9  | →           | RANGE                  | TOLERANCE |  |         |        | LMC        | SCALE             | NO  |             |      |
| 3  | →           | 8  | →           | X                      | ±0.30     |  |         |        | 2022.07.29 | MAT'L             | *** |             |      |
| 2  | →           | 7  | →           | X.X                    | ±0.20     |  |         |        |            | MATERIAL NO.      |     | DRAWING NO. | REV. |
| 1  | →           | 6  | →           | X.XX                   | ±0.10     |  |         |        |            |                   |     | WIF122058   | A0   |
| NO | DESCRIPTION | NO | DESCRIPTION | ANGLES                 | ±1°       | LEGION ELECTRONIC & HARDWARE CO., LTD. |         |        |            | MFR01-A1F02L1SN-B |     |             |      |