

Silicon N-Channel Power MOSFET

Description


MD40N25 the silicon N-channel Enhanced MOSFETs, is obtained by advanced MOSFET technology which reduce the conduction loss, improve switching performance and enhance the avalanche energy. The transistor is suitable device for SMPS, high speed switching and general purpose applications.

General Features

- ① $V_{DS}=250V$, $R_{ds(on)}<80m\Omega$ @ $V_{GS}=10V$, $I_D=40A$ (Typ:65mΩ)
- ② Fast Switching
- ③ Low C_{rss} (typical 18pF)
- ④ 100% avalanche tested
- ⑤ Improved dv/dt capability
- ⑥ RoHS product

Application

- ① High frequency switching mode power supply



Package Marking And Ordering Information:

| Ordering Codes | Package | Product Code | Packing |
|----------------|---------|--------------|---------|
| MD40N25 | TO-247 | MD40N25 | Tube |

ABSOLUTE RATINGS @ $T_a=25^\circ C$ (unless otherwise specified)

| Symbol | Parameter | Rating | Units |
|-----------|--|----------|-------|
| V_{DSS} | Drain-to-Source Voltage | 250 | V |
| I_D | Continuous Drain Current | 40 | A |
| | Continuous Drain Current $T_c = 100^\circ C$ | 26 | A |
| I_{DM} | Pulsed Drain Current(Note1) | 160 | A |
| V_{GS} | Gate-to-Source Voltage | ± 30 | V |
| E_{AS} | Single Pulse Avalanche Energy(Note2) | 2000 | mJ |
| dv/dt | Peak Diode Recovery dv/dt (Note3) | 5.0 | V/ns |



迈诺斯科技

MD40N25

| | | | |
|-----------------------------------|--|-----------------|------|
| PD | Power Dissipation | 310 | W |
| | Derating Factor above 25°C | 2.78 | W/°C |
| T _J , T _{stg} | Operating Junction and Storage Temperature Range | 150, -55 to 150 | °C |
| T _L | Maximum Temperature for Soldering | 300 | °C |

Thermal characteristics

Thermal characteristics TO-247

| Symbol | Parameter | RATINGS | Units |
|------------------|---------------------|---------|-------|
| R _{θJC} | Junction-to-Case | 0.36 | °C/W |
| R _{θJA} | Junction-to-Ambient | 62.5 | °C/W |

Electrical Characteristics at T_c = 25°C, unless otherwise specified

| OFF Characteristics | | | | | | |
|--------------------------------------|-----------------------------------|--|--------|-------|------|-------|
| Symbol | Parameter | Test Conditions | Values | | | Units |
| | | | Min. | Typ. | Max. | |
| V _{DSS} | Drain to Source Breakdown Voltage | V _{GS} =0V, I _D =250μA | 250 | -- | -- | V |
| ΔBV _{DSS} /Δ T _J | Bvdss Temperature Coefficient | ID=250μA, Reference 25 °C | -- | 0.18 | -- | V/°C |
| I _{DSS} | Drain to Source Leakage Current | V _{DS} =250V, V _{GS} =0V, T _j = 25 °C | -- | -- | 1 | μA |
| | | V _{DS} =200V, V _{GS} =0V, T _j = 125 °C | -- | -- | 10 | μA |
| I _{GSS(F)} | Gate to Source Forward Leakage | V _{GS} =+30V | -- | -- | 100 | nA |
| I _{GSS(R)} | Gate to Source Reverse Leakage | V _{GS} =-30V | -- | -- | -100 | nA |
| ON Characteristics | | | | | | |
| Symbol | Parameter | Test Conditions | Values | | | Units |
| | | | Min. | Typ. | Max. | |
| R _{DSON} | Drain-to-Source On- Resistance | V _{GS} =10V, I _D =20A(Note4) | -- | 0.065 | 0.08 | Ω |



迈诺斯科技

MD40N25

| | | | | | | |
|--------------|--------------------------|--|-----|----|-----|---|
| $V_{GS(TH)}$ | Gate Threshold Voltage | $V_{DS} = V_{GS}$, $ID = 250\mu A$ (Note4) | 2.0 | -- | 4.0 | V |
| g_{fs} | Forward Transconductance | $V_{DS}=40V$, $ID = 20A$ (Note4) | -- | 27 | -- | S |

Dynamic Characteristics

| Symbol | Parameter | Test Conditions | Values | | | Units |
|-----------|------------------------------|-----------------|--------|------|------|----------|
| | | | Min. | Typ. | Max. | |
| R_g | Gate resistance | $f = 1.0MHz$ | -- | 1.8 | -- | Ω |
| C_{iss} | Input Capacitance | $V_{GS} = 0V$ | -- | 3700 | -- | PF |
| C_{oss} | Output Capacitance | $V_{DS} = 25V$ | -- | 360 | -- | |
| C_{rss} | Reverse Transfer Capacitance | $f =$ | -- | 2.5 | -- | |

Switching Characteristics

| Symbol | Parameter | Test Conditions | Values | | | Units |
|--------------|--------------------------------|---|--------|------|------|-------|
| | | | Min. | Typ. | Max. | |
| $t_{d(ON)}$ | Turn-on Delay Time | $I_D = 40A$ $VDD = 125V$ $VGS = 10V$ $RG = 15\Omega$ | -- | 80 | -- | ns |
| t_r | Rise Time | | -- | 620 | -- | |
| $t_{d(OFF)}$ | Turn-Off Delay Time | | -- | 140 | -- | |
| t_f | Fall Time | | -- | 183 | -- | |
| Q_g | Total Gate Charge | $ID = 40A$ $VDD = 200V$ $VGS = 10V$ | -- | 40 | -- | nC |
| Q_{gs} | Gate to Source Charge | | -- | 14 | -- | |
| Q_{gd} | Gate to Drain ("Miller")Charge | | -- | 11 | -- | |

Source-Drain Diode Characteristics

| Symbol | Parameter | Test Conditions | Values | | | Units |
|----------|--|---|--------|------|------|-------|
| | | | Min. | Typ. | Max. | |
| I_s | Continuous Source Current (Body Diode) | $TC=25^{\circ}C$ | -- | -- | 40 | A |
| I_{SM} | Maximum Pulsed Current (Body Diode) | | -- | -- | 160 | A |
| V_{SD} | Diode Forward Voltage | $IS=40A$, $VGS=0V$ (Note4) | -- | -- | 1.2 | V |
| T_{rr} | Reverse Recovery Time | $IS=40A$, $T_j = 25^{\circ}C$ $dI/dt=100A/us$, $VGS=0V$ | -- | 230 | -- | ns |
| Q_{rr} | Reverse Recovery Charge | | -- | 2150 | -- | nC |

Note1: Pulse width limited by maximum junction temperature

Note2: $L=10mH$, $VDs=50V$, Start $TJ=25^{\circ}C$

Note3: $ISD = 40A$, $di/dt \leq 100A/us$, $VDD \leq BVDS$, Start $TJ=25^{\circ}C$

Note4: Pulse width $tp \leq 300\mu s$, $\delta \leq 2\%$



迈诺斯科技

MD40N25

Characteristics Curves




Figure 4 Typical Output Characteristics




Figure 5 Typical Transfer Characteristics




Figure 6 Typical Drain to Source ON Resistance vs Drain Current




Figure 7 Typical Drian to Source on Resistance vs Junction Temperature









Figure 8 Typical Threshold Voltage vs Junction Temperature

Figure 9 Typical Breakdown Voltage vs Junction Temperature

Figure 10 Typical Capacitance vs Drain to Source Voltage

Figure 11 Typical Gate Charge vs Gate to Source Voltage


Test Circuit and Waveform

| Gate Charge Test Circuit | Gate Charge Waveforms |
|-------------------------------------|---------------------------------|
| | |
| Resistive Switching Test Circuit | Resistive Switching Waveforms |
| | |
| Diode Reverse Recovery Test Circuit | Diode Reverse Recovery Waveform |
| | |

| Unclamped Inductive Switching Test Circuit | Unclamped Inductive Switching Waveform |
|--|--|
| | |

Package Description



| Items | Values(mm) | |
|-------|------------|-------|
| | MIN | MAX |
| A | 4.6 | 5.2 |
| A1 | 2.2 | 2.6 |
| B | 0.9 | 1.4 |
| B1 | 1.75 | 2.35 |
| B2 | 1.75 | 2.15 |
| B3 | 2.8 | 3.35 |
| B4 | 2.8 | 3.15 |
| C | 0.5 | 0.7 |
| D | 20.60 | 21.30 |
| D1 | 16 | 18 |
| E | 15.5 | 16.10 |
| E1 | 13 | 14.7 |
| E2 | 3.80 | 5.3 |
| E3 | 0.8 | 2.60 |
| e | 5.2 | 5.7 |
| L | 19 | 20.5 |
| L1 | 3.9 | 4.6 |
| ΦP | 2.5 | 3.70 |
| Q | 5.2 | 6.00 |
| S | 5.8 | 6.6 |

TO-247 Package



迈诺斯科技

MD40N25

NOTE:

1. Exceeding the maximum ratings of the device in performance may cause damage to the device, even the permanent failure, which may affect the dependability of the machine. Please do not exceed the absolute maximum ratings of the device when circuit designing.
2. When installing the heat sink, please pay attention to the torsional moment and the smoothness of the heat sink.
3. MOSFETs is the device which is sensitive to the static electricity, it is necessary to protect the device from being damaged by the static electricity when using it.
4. Shenzhen Minos reserves the right to make changes in this specification sheet and is subject to change without prior notice.

CONTACT:

深圳市迈诺斯科技有限公司（总部）

地址：深圳市福田区华富街道田面社区深南中路4026号田面城市大厦22B-22C

邮编：518025

电话：0755-83273777