

# 158-A-111

# PCB connector Screw connection



# GENERAL INFORMATION


Pitch	10,16 mm
No. of poles	2 - 12
Usable with	158-A-211, 159-A-111 and 159-A-211, mountable side-by-side to any series connector
Areas of application	Power electronics, in particular for drives with frequency converters, and also for power supplies and charging units.
Additional Information	Hole for ø 2 mm test plug


# TECHNICAL DATA


Clamping Range	solid / stranded / AWG					
	0,5 - 16 mm <sup>2</sup> / 0,5 - 10 mm <sup>2</sup> / 20 - 6 AWG					
Rated Cross Section	10 mm <sup>2</sup>	10 mm²				
Wire Stripping Length	10,5 mm ± 1 mm	10,5 mm ± 1 mm				
Overvoltage Category	III	III	II			
Pollution Severity Level	3	2	2			
Rated Voltage	690 V	1000 V	1000 V			
Rated Impulse Voltage	8 kV	8 kV	6 kV			
Rated Current	57 A					
Hole in PCB	ø 1,5 mm					
Torque	1,2 Nm					
Other specifications	Maximum current/cross-section 76 A / 16 mm <sup>2</sup> , stranded wire					

#### APPROVALS

	Current [A]	Voltage [V]	Group	AWG	[Nm]
c <b>911</b> ®us	60 10	300 300	B, C D	20 - 6 20 - 6	1,3 1,3
	Current [A]	Voltage [V]	mm²		
Ď <sup>V</sup> E	57	690 - 1000 [1]	2,5 - 10		







### **MATERIAL**

Moulding	PA, grey, V-0
Comparative Tracking Index	CTI ≥ 600
Insulating Group	I
Temperature Range	-40°C up to 100°C
Terminal body	Nickel plated brass
Pressure clamp	Tin plated copper
Screw	Plus-minus, M4; zinc plated steel, blue passivated
Solder pin	Tin plated copper

## OPTIONS / ACCESSORIES

- · Consecutive numbering
- Special marking according to drawing
- Self-adhesive marking strip BST-10,16

[1] Marks approval acc. to DIN EN 60947-7-4

## CONFIGURATIONS

Poles Part number	Article number	Length (L)	Packaging	PU
2 158-A-111/02	12.801.901	20,32 mm	Box	50
3 158-A-111/03	13.801.901	30,48 mm	Box	50
4 158-A-111/04	14.801.901	40,64 mm	Box	50
5 158-A-111/05	15.801.901	50,80 mm	Box	50
further number of poles on request				



