



REV.	ECN NO.	REVISED	DATE






NOTE:

1.MATERIAL:


- a.HOUSING:PA9T BLACK
- b.CONTACTS:H62 (SURFACE PLATING: Au1u")
- C.SRSPRINGS: STAINLESS STEE (SURFACE PLATING: Au1u")
- SEE ORDERING INFORMATION

2.ELECTRIC:

- a.CONTACT RESISTANCE: 30 MILLIOHMS MAX
- b.INSULATION RESISTANCE: 100 MEGA OHMS MIN
- c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE
- d.OPERATING TEMPERATURE: -25°C~ +85°C



PCB Layout Diagram  
Top View



ORDERING INFORMATION  
BH-AAA-B5AA033

电池盒  
电池型号  
SMT 180° TYPE

PLATING:  
A-Au1U"  
J-Ni100U"~120U"  
K-Sn100U"~120U"

MATERIAL:  
1A-PBT BLACK  
1B-PA66 BLACK  
2A-PPA BROWN  
2B-PPA BLACK  
3A-PPS BROWN  
3B-PPS BLACK  
4A-LCP WHITE  
4B-LCP BLACK  
5A-PA9T BLACK

工程部  
2023-09-13  
H. WANG

4	SPRING	2	STAINLESS STEEL DIA=0.5	Au(1u")-Plating
3	TERMINAL-	2	H62 T=0.3mm	Au(1u")-Plating
2	TERMINAL+	2	H62 T=0.3mm	Au(1u")-Plating
1	HOUSING	1	PA9T BLACK	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		<b>MYOUNG 美用</b> <a href="http://www.meiyangdz.com">www.meiyangdz.com</a>	
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND	Huanglieqing
WEIGHT:		DATE	2023-09-13
SHEET 1 OF 1		CHKD	ZhouRuicai
		DATE	2023-09-13
		APVD	XueShunyong
		DATE	2023-09-13
		SCALE:	VIEW:
		SIZE: A4	TITLE:
		REV.: A/0	电池盒BH-AAA-2J Au SMT 负极弹簧
		OBJECT: MY	PART NO.:
			BH-AAA-B5AA033
			DRAW NO.:MY-CP-0377