

Surface Mount Schottky Rectifier

Features

- Guardring for overvoltage protection
- Low power loss
- Extremely fast switching
- High forward surge capability
- High frequency operation
- Solder dip 260 °C max. 10 s, per JESD 22-B106



Typical Applications

For use in low voltage high frequency inverters, freewheeling, DC/DC converters, and polarity protection applications.

Mechanical Data

- **Package:** DO-214AB (SMC)
Molding compound meets UL 94 V-0 flammability rating, RoHS-compliant
- **Terminals:** Tin plated leads, solderable per J-STD-002 and JESD22-B102
- **Polarity:** Color band denotes the cathode end

DO-214AB (SMC)



Unit : inch(mm)



■ Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	SS1020	SS1030	SS1040	SS1050	SS1060	SS1080	SS10100	SS10150	SS10200	
Repetitive Peak Reverse Voltage	V_{RRM}	V	20	30	40	50	60	80	100	150	200	
Average Rectified Output Current @60Hz sine wave, Resistance load, TL (FIG.1)	I_O	A	10.0									
Surge(Non-repetitive)Forward Current @60Hz Half-sine wave, 1 cycle, Ta=25°C	I_{FSM}	A	120									
Storage Temperature	T_{stg}	°C	-55 ~+150									
Junction Temperature	T_j	°C	-55 ~+150					-55 ~+175				

■ Electrical Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	TEST CONDITIONS	SS1020	SS1030	SS1040	SS1050	SS1060	SS1080	SS10100	SS10150	SS10200
Maximum instantaneous forward voltage drop per diode	V_F	V	$I_{FM}=10.0A$	0.55			0.70	0.85		0.95		
Maximum DC reverse current at rated DC blocking voltage per diode	I_R	mA	Ta=25°C	0.2					0.1			
			Ta=100°C	20					5.0			

■ Thermal Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	SS1020	SS1030	SS1040	SS1050	SS1060	SS1080	SS10100	SS10150	SS10200
Thermal Resistance	Between junction and ambient	$R_{\theta JA}$	65 ⁽¹⁾								
	Between junction and lead	$R_{\theta JL}$	8 ⁽¹⁾								

Note (1)

Thermal resistance from junction to ambient and from junction to lead mounted on P.C.B. with 0.6" x 0.6" (16 mm x 16 mm) copper pad areas



■ Characteristics (Typical)

FIG.1: Io-TL Curve




FIG.2: Forward Surge Current Capability




FIG.3: Forward Voltage




FIG.4: Typical Reverse Characteristics

