CTCDRH3D28F Series From 3.3 µH to 47 µH




CHARACTERISTICS


Description: SMD (shielded) power inductor.
Applications: Power supplies for OA equipment, LCD televisions, PC notebooks, portable communication equipment, DC/DC converters, etc.
Operating Temperature: -40°C to +85°C Inductance Tolerance: ±20%, ±30%
Testing: Inductance is tested on an HP4285A at 100KHz, 0.1V Packaging: Tape & Reel.
Marking: Parts are marked with letter identifier.
Miscellaneous: RoHS Compliant.
Additional Information: Additional electrical & physical information available upon request.
Samples available. See website for ordering information.

SPECIFICATIONS

	Part numbers indicate available inductance tolerance: $M = \pm 20\%, N = \pm 30\%$ Inductance drop = 35% typ. at Isat. $\Delta T=40^{\circ}C$ rise at Irms.								
Part Number	Marking	Inductance at 100kHz (µH)	Irms Max. (A)	Isat Max. (A)	DCR Max. (Ω)				
CTCDRH3D28F-3R3N CTCDRH3D28F-4R7N CTCDRH3D28F-6R8N	D E F	3.30 4.70 6.80	1.85 1.62 1.32	2.00 1.65 1.24	0.0721 0.0883 0.1190				
CTCDRH3D28F-100M CTCDRH3D28F-150M CTCDRH3D28F-220M CTCDRH3D28F-330M CTCDRH3D28F-470M	G K M O	10.0 15.0 22.0 33.0 47.0	1.18 1.02 0.74 0.63 0.56	1.05 0.90 0.76 0.58 0.48	0.1450 0.2130 0.3350 0.4810 0.5990				

PHYSICAL DIMENSIONS							
Size	A Max.	B Max.	C Max.	D Max.	E Ref.		
mm	4.0	4.0	3.0	5.2	1.0		
inches	0.16	0.16	0.12	0.20	0.04		





PAD LAYOUT

