

P1AT-29MF-40G2W-10

RF Attenuator, 2.92mm Male to 2.92mm Female, 10 dB, 2 W. Frequency DC to 40 GHz
with a 1.25 max VSWR.

Product Features

P1AT-29MF-40G2W-10 is a 50 Ohm RF fixed value attenuator, frequency DC to 40 GHz.

2.92mm male to 2.92mm female connectors. Attenuation 10 dB.

Power handling is 2 Watts. Max VSWR is 1.25.

Attenuator body is passivated stainless steel.



Electrical Specification: $T_{\text{Ambient}} = 25^{\circ}\text{C}$

| Parameter | Frequency Range | Units | Min | Typical | Max | Notes |
|-----------------|-----------------|-------|-----|---------|------|-------|
| Frequency Range | | GHz | DC | | 40.0 | |



Mechanical And Environmental Specifications:

| Parameter | Description | Notes |
|-----------------|---------------|-------|
| Connector 1 | 2.92mm Male | |
| Connector 2 | 2.92mm Female | |
| RoHS Compliance | Yes | |

Drawing

P1AT-29MF-40G2W-10

RF Attenuator, 2.92mm Male to 2.92mm Female, 10 dB, 2 W. Frequency DC to 40 GHz with a 1.25 max VSWR.



Product Notes