


NOTE:

1. Rating: DC12V 50mA;
2. Contact Resistance: 100mΩ Max;
3. Insulation Resistance: 100MΩ Min;
4. Withstanding Voltage: AC250V For 1 Minute;
5. Life Cycle: 50,000 Cycle Min;
6. Operating Force: 260±50gf;
7. Travel: 0.4±0.15mm.



Circuit Diagram

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED							
6	SHELL	PA66	1	BLACK	UP TO 5mm: ±0.1	ANGULAR	1					
5	SHRAPNEL	COPPER ALLOY	1	Ag-Plated	ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS			BY APPD
4	TERMINAL	BRASS	2	Ag-Plated	TITLE: TACT SWITCH			UNIT : MM	ROHS COMPLIANT	DWN		
3	COVER	SPCC	1	Ni-Plated	MODEL: TC-00120-120E			SCALE: 1:1	COMPLIANT	CHK'D		
2	KNOB	PPA	1	BLACK	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司					APPD		
1	BASE	PPA	1	BLACK				PRO.AGL:			REV :A0	