





NOTE:

1. Rating: DC12V 50mA;
2. Contact Resistance: 100mΩ Max;
3. Insulation Resistance: 100MΩ Min;
4. Withstanding Voltage: AC250V For 1 Minute;
5. Life Cycle: 100,000 Cycle Min;
6. Operating Force: 160±50/250±50gf;
7. Travel: 0.15±0.1mm.



Circuit Diagram



PCB LAND PATTERN

				TOLERANCE UNLESS SPECIFIED							
				UP TO 5mm: ±0.1	ANGULAR						
				ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
6											
5	SHRAPNEL	SUS	1	Ag Plated	TITLE: TACT SWITCH		UNIT : MM	ROHS COMPLIANT	DWN		
4	TERMINAL	BRASS	1	Ag Plated	MODEL: TS-1183U-025C		SCALE: 1:1		CHK'D		
3	COVER	SUS	1	Ni Plated	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司				APPD		
2	KNOB	PA9T	1	BLACK			PRO.AGL:		REV :A0		
1	BASE	LCP	1	BLACK							
NO.	PART NAME	MATERIAL	QTY	FINISHING							