



## **FEATURES**

- Wideband:
- NF (ext match): 1.2 dB @ 2.0 GHz
  - 1.6 dB @ 6.0 GHz 1.8 dB @ 12.0 GHz
- P-1dB: 16 dBm
- OIP3: 27 dBm
- Gain: 17 dB
- Bias Condition: VDD = 5 V IDD = 55 mA
- 50-Ohm On-chip Matching
- Unconditionally Stable: .5 GHz to 20 GHz
- Unconditionally Stable: .5 GHz to 20 GHz
- Narrow-Band Optimization with External Tuning
  Cain Control Option Available with 2nd Cate Control V
- Gain Control Option Available with 2nd Gate Control Voltage

1.0 to 12 GHz

## DESCRIPTION

## APPLICATIONS

- Microwave Point-to-Point Radios
- Satellite and Telemetry Communications
- Test Instrumentation
- EW Receiver Systems
- Wide-band Communication Systems
- Commercial Wireless Systems

The MLA-01122B is a fully-matched broadband Low-Noise MMIC amplifier utilizing high-reliability low-noise GaAs PHEMT technology. This MMIC is suited for Satellite Communications, Microwave radios, Instrumentation, Wideband Systems and also many commercial wireless applications where low-noise figure with high-gain is desirable. It has excellent gain (17 dB) and Noise Figure (1.6 dB, mid-band) over a broad frequency range. Typical P-1dB is 16.5 dBm and OIP3 is +27dBm @ 6 GHz. It has on-chip bias circuit, choke and DC blocking to provide bias stability and ease of use. The 2<sup>nd</sup> Gate voltage input can be used for gain control if necessary. For packaged options, contact factory for further details.

## ELECTRICAL SPECIFICATIONS: VDD=+5.0V, VG1=+0.15V, VG2=+2V, IDD=55 mA, Ta=25 C, ZO=50 ohm <sup>(1)</sup>

PARAMETER	TEST CONDITIONS	TYPICAL DATA	UNITS
Frequency Range		1-12	GHz
Gain	1 - 8 GHz	17	dB
	10 - 12 GHz	19	
Gain Flatness	1 - 8 GHz	0.6	+/-dB
	1 - 12 GHz	1.5	
	2 GHz	15	
Input Return Loss	5 GHz	9.5	dB
	10 GHz	12	
Output Return Loss		12	dB
Output P1dB	2 GHz	17	d B m
	6 GHz	16.5	
	10 GHz	15.5	
	12 GHz	14.0	
	2 GHz	30	
@ 0 dBm/tone, 1 MHz separation	6 GHz	27	dBm
	12 GHz	25	
Noise Figure	2 GHz	1.2	
	6 GHz	1.6	dB
	12 GHz	1.8	
Operating Bias Conditions: VDD IDD	VG1=+0.15V, VG2=+2V	+5	V
		55	mA
Stability Factor K	0.5 to 20 GHz	> 1	

(1) All data is measured on 50 Ohm carrier with VG2 bias derived from VDD bias using resistive voltage divider and external tuning stubs show n in assembly diagram.



- - - - Output

4 5 6 7 8 9 10 11 12 13 14

**Return Loss versus Frequency** 

Input

0

-5

-10

-15

-20

0 1

2 3

Return Loss (dB)



**Isolation versus Frequency** 

Frequency (GHz)

6 7 8 9 10 11 12 13 14

0

-10

-20

-30

0 1

2 3

4 5

Isolation (dB)

### TYPICAL RF PERFORMANCE: VDD=+5.0V, VG1=+0.15V, VG2=+2V, IDD=55 mA, Ta=25 C, ZO=50 ohm <sup>(1)</sup>



Frequency (GHz)





MicroWave Technology, Inc., 4268 Solar Way, Fremont, CA 94538 510-651-6700 FAX 510-952-4000 WEB <u>www.mwtinc.com</u> Data contained herein is subject to change without notice. All rights reserved © Please visit MwT website <u>www.mwtinc.com</u> for information on other MwT MMIC products. Page 2 of 4, Updated July 2017



## ASSEMBLY DIAGRAM: For use with on-chip match option

50-Ohm Microstrip Line 50-Ohm Microstrip Line B ## em 🖂 ٦ O VGI VG2 V00 Tuning Stub Tuning Stub 7Š0pF 750pF 750pF 0.01uF 0.01uF 0.01uF VG1 VG2 VDD

### Notes:

- 1<sup>st</sup> Close-in Bypass cap values must be at least 100pF and placed < 25mil from chip edge. The location of large bypass cap 0.01uF is not critical but recommended close to die. VG1 & VG2 large bypass cap 0.01uF may be removed to save space.
- 2) VG2 voltage may be derived from VDD supply using resistive voltage divider
- 3) RF IN/OUT Bonds must be 2 wires of length < 20 mil & 0.7 mil diameter for best RF performance.
- 4) Tuning stubs (10 x 40 mil) on the 50 ohm line will improve wide-band I/O return loss especially at frequencies > 8 GHz. Location may be tuned for best RF performance. All data shown includes the tuning stubs. Input Return Loss can be further optimized for narrower frequency band.

## **ABSOLUTE MAXIMUM RATINGS**

SYMBOL	PARAMETERS	UNITS	MAX
VDD	Drain Voltage	V	7
IDD	Drain Current	mA	75
Pdiss	DC Pow er Dissipation	W	0.4
Pin max	RF Input Pow er	dBm	13
Toper	Operating Case/Lead Temp Range	°C	-40 to +85
Tch	Channel Temperature	°C	150
Tstg	Storage Temperature	°C	-60 to 150

Exceeding any on of these limits may cause permanent damage.



# **MLA-01122B** 1 - 12 GHz Low-Noise MMIC Amplifier Data Sheet

## **MECHANICAL INFORMATION**



#### Notes:

- 1) Die Size: 1.57 x 1.31 x 0.1 mm
- 2) RFIN, RFOUT, VG1, VG2 Bond Pad Size is: 80 x 80 micron.
- 3) Backside of chip is metalized and provides DC & RF Ground.
- 4) Bond Pad & Backside metallization: Gold



P (510) 651-6700 F (510) 952-4000 www.mwtinc.com



MicroWave Technology, Inc., 4268 Solar Way, Fremont, CA 94538 510-651-6700 FAX 510-952-4000 WEB <u>www.mwtinc.com</u> Data contained herein is subject to change without notice. All rights reserved © Please visit MwT website <u>www.mwtinc.com</u> for information on other MwT MMIC products. Page 4 of 4, Updated July 2017