

DIMENSIONS (in.)					
No. OF PINS	A	B	C	D	Insulator Material
15	0.642	0.984	1.213	0.090	PA9T
26	0.969	1.311	1.543	0.090	PA9T
44	1.512	1.852	2.089	0.090	PA9T
62	2.157	2.500	2.732	0.095	PA6T

DIMENSIONS (mm)					
No. OF PINS	A	B	C	D	Insulator Material
15	16.30	25.00	30.80	2.29	PA9T
26	24.60	33.30	39.20	2.29	PA9T
44	38.40	47.05	53.05	2.29	PA9T
62	54.80	63.50	69.40	2.41	PA6T

MATERIALS AND FINISH:

SHELL: STEEL MATERIAL, NICKEL FINISH
 INSULATOR: (SEE DIM. CHART) = 260°C PROCESS TEMP, UL 94V-0 RATED, BLACK
 CONTACT MATERIAL: BRASS
 CONTACT FINISH: SEE PLATING PART NUMBER KEY BELOW

ELECTRICAL:

CONTACT CURRENT RATING: 3 AMPS
 CONTACT RESISTANCE: 10 mOHMS Max.
 DIELECTRIC WITHSTANDING VOLTAGE: 1,000VAC Min.
 INSULATION RESISTANCE: 5 GOHMS Min.
 TEMPERATURE RATING: -55° ~ +125° C

180-MYY-2YYRYYY

SERIES ————
 MACHINED CONTACTS ————
 POSITIONS ————
 15
 26
 44
 62
 GENDER ————
 2 = FEMALE
 CONTACT LENGTH ————
 1 = 0.256"
 A = 0.140"
 SHELL PLATING ————
 3 = NICKEL

HARDWARE OPTIONS ————
 00 = NO HARDWARE, Ø.120" HOLE
 01 = .098" CLINCH NUT (BOARD SIDE)
 02 = .236" CLINCH NUT (BOARD SIDE)
 03 = .236" CLINCH NUT (MATING SIDE)
 05 = .224" BOARD LOCK (BOARD SIDE)
 S5 = .237" BOARD LOCK (BOARD SIDE)
 91 = .224" 4-40 SPACER/BOARD LOCK
 92 = .237" 4-40 JACK SCREW // BOARD LOCK (.093" PCB)

PLATING OPTIONS ————
 1 = GOLD FLASH, ENTIRE CONTACT
 2 = 30u" GOLD, ENTIRE CONTACT
 3 = 50u" GOLD, ENTIRE CONTACT

RoHS COMPLIANT

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NC

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.


DRAWN: C. SMITH
 DATE: 03/16/2007

NorComp


SCALE: NTS SHEET 1 OF 3 REV 28
 DWG NO. 180-MYY-21YRYYY

ALL CLINCH-NUTS ARE 4-40 INTERNAL THREADS


01 0.098" BOARD SIDE




02 0.236" BOARD SIDE




03 0.236" MATING SIDE




05 0.224" BOARD SIDE




S5 0.237" BOARD SIDE



91 0.224" BOARD SIDE
0.189" MATING SIDE



92 0.237" BOARD SIDE
0.189" MATING SIDE



NOTE: 4-40 FEMALE SCREW LOCK IS REMOVABLE

05, S5, AND 91 HARDWARE OPTIONS DESIGNED TO BE USED WITH STANDARD THICKNESS PCB (APPROX. 0.063")

NOTE: 4-40 FEMALE SCREW LOCK IS REMOVABLE

RoHS COMPLIANT

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH

DATE:
03/16/2007

NorComp





SCALE:
NTS

SHEET OF
2 3

REV
28

DWG NO.

180-MYY-21YRYYY



HOLE PATTERN SHOWN ARE FOR FEMALE

* TYP. SUGGESTED SIZE MAY NOT BE SUITABLE FOR ALL APPLICATIONS

RoHS COMPLIANT

UNITS = inch

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: C. SMITH
DATE: 03/16/2007

NorComp

SCALE: NTS	SHEET 3 OF 3	REV 28
DWG NO. 180-MYY-21YRYYY		