





# SCPH73

## SMD POWER INDUCTORS





### • Features

1. Magnetically shielded construction
2. Excellent Power Density
3. Engineered to Provide High Efficiency

## ELECTRICAL CHARACTERISTICS



Part Number	Inductance (uH) (1)	Test Frequency	DC Resistance (Ω MAX) (2)	Saturation Current (A) <sup>(3)</sup>	Temperature Current (A) <sup>(4)</sup>
SCPH73-100	10	1KHZ	90m	1.40	2.00
SCPH73-120	12	1KHZ	0.10	1.30	1.80
SCPH73-150	15	1KHZ	0.13	1.20	1.62
SCPH73-180	18	1KHZ	0.15	1.10	1.54
SCPH73-220	22	1KHZ	0.17	1.00	1.38
SCPH73-270	27	1KHZ	0.21	0.88	1.30
SCPH73-330	33	1KHZ	0.24	0.80	1.23
SCPH73-390	39	1KHZ	0.31	0.75	1.16
SCPH73-470	47	1KHZ	0.35	0.67	1.10
SCPH73-560	56	1KHZ	0.40	0.62	0.89
SCPH73-680	68	1KHZ	0.52	0.54	0.84
SCPH73-820	82	1KHZ	0.60	0.52	0.80
SCPH73-101	100	1KHZ	0.70	0.46	0.68
SCPH73-121	120	1KHZ	0.82	0.42	0.61
SCPH73-151	150	1KHZ	1.35	0.37	0.54
SCPH73-181	180	1KHZ	1.50	0.33	0.48
SCPH73-221	220	1KHZ	1.70	0.30	0.43
SCPH73-271	270	1KHZ	1.90	0.28	0.40
SCPH73-331	330	1KHZ	2.80	0.25	0.34
SCPH73-391	390	1KHZ	3.00	0.22	0.32
SCPH73-471	470	1KHZ	3.50	0.20	0.30



(1). Inductance tolerance ±20% tested at 0.25V, 0ADC and 25°C

(2). DCR measured at 25°C.

(3). The DC current at which the inductance decreases by 35% from its initial value.

(4). The DC current that results in a 40°C temperature rise from 25°C ambient.

[Click here for QUANTITY PER REEL & PACKING INFORMATION](#)

Custom versions available upon request.

© 2019 Signal Transformer –Specification subject to change without notice. 12.19