

SPECIFICATION FOR APPROVAL

規 格 書

Customer (客戶名稱): _____

Customer P/N(客戶番號): _____

Our P/N (本廠番號): FS87W08100-H34

Approval Date(日期): 2020.6.18

Environment Request(環境標準):

Non-RoHS (非 RoHS 標準)

RoHS (RoHS 標準)

REACH (REACH 標準)

Others (其他)

CUSTOMER'S APPROVED SIGNATURE

--	--	--



泰州福聲電子科技有限公司

Taizhou Fusheng Electronic Technology Co.,Ltd.

Adds: No168 of FengHuang Road West,Hailing District ,Taizhou .

地址：江蘇省泰州市海陵區鳳凰西路98號

Tel: +86-523-86219066

Fax: +86-523- 81601108

[Http://www.tzfsdz.com](http://www.tzfsdz.com)




E-mail: sales@electronic-tech.cn

	DESINGER	CHECKED	APPROVED
SIGNATURE			
DATE			

Speaker Specification

Part No.	Customer No 顧客型號		Customer code 顧客編號	
	Our Part No 本廠編號	FS87W08100-H434		Revision 版本 B
No.	Item 項目	Specification 規格	Testing Condition 測試條件	
1.	Rated Imp 共稱阻抗	8ohm±15%	At 1kHz8.94Vrms	
2.	Resonance Freq 最低共振周波數	620Hz±20%	Without Baffle	
3.	Output S.P.L. 出力音壓	90±3dB	At 1m 1w ,0.8,1.0,1.2,1.8KHz Average	
4.	Rated Power 定格入力	at 10.0W	at 8.94 Vrms	
5.	Max Power 最大入力	at 15.0W	at 10.95 Vrms	
6.	Frequency Range 實效頻寬	FO----6kHz		
7.	Operation 可靠性試驗	Must Be Normal at Rated Frequency Range	Program Source 10W FO ----- 10kHz	
8.	Buzzes & Rattles 異常音試驗	Should not be audible buzz and rattle at Rated Frequency Range 無異常聲	Sine Wave Between (正弦波入力) at 8.94 Vrms / FO---- 10kHz	
9.	T H D 失真	≤5%		
10.	Magnet 磁鐵	Ferrite		
11.	Operating Temperature 動作溫度	-30°C to +60°C		
12.	Storage Temperature 儲存溫度	-40°C to +65°C		
13.	Weight 重量	271g±8%		


Product Outside View



产品图片Picture:




Frequency Response



Remark

NO	零件Component	材质Material
1	压边 Gasket	橡胶压边Rubber
2	盆架 Frame	冷轧钢板SPCC
3	音圈 Voice coil	铝管+铜 ASV+Cu
4	弹波 Damper	塑料 PET
5	华司Washer	冷轧钢板SPCC
6	磁铁 Magnet	铁氧体Ferrite
7	T铁 T-yoke	冷轧钢板 SPCC
8	鼓纸 Cone	防水盆 PET
9	帽子 Dust cap	防水帽 PET
10	接线板 Terminals	纸板+铁Paper+steel

包装 Packing picture:



1. Each clapboard 24 pcs,
Each carton 2 clapboards,
48 pcs/carton
2. N.W: 13 KG, G.W:15KG
3. Corrugated paper: 365*325 mm 1pcs
4. Carton size: 380*340*220 mm 1 pcs

