




SPECIFICATION

1. Rating : DC 50V 0.3A.
2. Function: 4P2T
3. Contact resistance: $\leq 100\text{m}\Omega$.
4. Insulation resistance: $\geq 100\text{M}\Omega$ (DC500V).
5. Withstanding voltage: 500VAC .
6. Operating Force: $350 \pm 100\text{gf}$.
7. life test: 10,000 cycles.
8. Operation temperature range: $-25^\circ\text{C} \sim 85^\circ\text{C}$.
9. Sign"* "is importance dimension.

| | | | | | | | | | | | |
|-----|--------------|---------------|----------|-----------|-----------------------|--|------------|-----------|---|---------|------|
| 9 | SPRING PLATE | PBS STRIP | 1 | NATURAL | | | | | | | |
| 8 | CONTACT CLIP | PBS C5210R-EH | 4 | Ag CLAD | TOLERANCE | | | | | | |
| 7 | CAM STICK | BRASS WIRE | 1 | Ni PLATED | UNLESS SPECIFIED | | | | | | |
| 6 | TERMINAL | BRASS STRIP | 12 | Ag PLATED | UP TO 5mm: ±0.1 | ANGULAR | | | | | |
| 5 | BASE | PPA | 1 | BLACK | ABOVE 5mm: ±0.2 | ±1° | NO | DATE | REVISIONS | BY | APPD |
| 4 | COVER | PC | 1 | BLUE | TITLE: PUSH SWITCH | | UNIT : MM | ROHS | DWN | | |
| 3 | SPRING | STEEL WIRE | 1 | Ni PLATED | MODEL: PS-909L-42C(L) | | SCALE: 1:1 | COMPLIANT | CHK'D | | |
| 2 | BLOCK | STEEL STRIP | 1 | Ni PLATED | | | | | APPD | | |
| 1 | KNOB | PA66 | 1 | BLACK | | | | | | | |
| NO. | PART | NAME | MATERIAL | QTY | FINISHING |  DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司 | | PRO.AGL: |   | REV :A0 | |