




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/11/08	
A		REVISED SHAPE	11/18/10	
B		REVISED COLOR	5/27/11	



CIRCUIT1

Positions: 2 thru 10, 12, 15, 20, 25, 30
 A = .049 [1.25] X No. of positions - 1
 B = .049 [1.25] X No. of positions + .077 [1.95]

SPECIFICATIONS:

Material:
 Insulator: Nylon 66, rated UL 94V-0
 Insulator color: Beige

Electrical:
 Voltage rating: 100V AC/DC
 Current rating: 1A AC/DC max
 Insulation resistance: 500 Mohms min
 Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
 Operating temperature: -25°C to +85°C
 Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			
INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010
APPROVALS		DATE	
DRAWN	SS	11/11/08	
CHECKED			
APPROVED			

ADAM TECH
 909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: 1.25mm CRIMP HOUSING SINGLE ROW
 2 THRU 30 POSITIONS, COLOR: BEIGE

SIZE X	PART NO. 125CH-D-XX	REV. B
REF: S00123T	SCALE: NTS	SHEET 1 OF 1

6 5 4 3 2 1

6 5 4 3 2 1

D

D

C

C

B

B

A

A