





APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



Wire Size AWG	Positions			
	2	4, 6	8, 10	12~24
#18	9A	8A	7A	6A
#20	7A	6A	5A	5A
#22	5A	4A	4A	4A
#24	4A	3A	3A	3A



**SPECIFICATIONS:**

**Material:**  
 Insulator: Nylon 66, rated UL 94V-2  
 Insulator color: Natural  
**Electrical:**  
 Operating voltage: 600 VAC max  
 Current rating: See chart  
 Insulation resistance: 1000 Mohms min @ 500 VDC  
 Dielectric withstanding voltage: 1500 VAC for 1 minute  
**Mechanical:**  
 Wire size: 18 Awg thru 24 Awg  
 Temperature Rating:  
 Operating temperature: -40°C to 105°C  
**Environmental:**  
 Lead free, RoHS compliant.

Positions: 2 thru 24  
 A = .165 [4.20] X No. of Spaces per row  
 B = .165 [4.20] X No. of Positions per row + .047 [1.20]  
 C = .165 [4.20] X No. of Positions per row + .063 [1.60]

UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE MM [INCHES]  
 TOLERANCES: EXCEPT AS NOTED  
 INCHES Holes  
 .X ± .10 ØXX ± .10  
 .XX ± .020 ØXXX ± .015  
 .XXX ± .015 ØXXXX ± .010

**ADAM TECH**  
 909 Railway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: PLUG HOUSING, DUAL ROW, .165 [4.20] PITCH

DRAWN	DY	9/23/08	SIZE	PART NO.	REV.
CHECKED			X	DMF-XX-W	A
APPROVED			REF:	S00123T	SHEET 1 OF 1

