CLL914

SURFACE MOUNT HIGH SPEED SILICON SWITCHING DIODE



www.centralsemi.com

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CLL914 type is an ultra-high speed silicon switching diode manufactured by the epitaxial planar process, in a hermetically sealed glass surface mount package, designed for high speed switching applications.

MARKING: CATHODE BAND



MAXIMUM RATINGS: (T _A =25°C)	SYMBOL		UNITS
Continuous Reverse Voltage	v_R	75	V
Peak Repetitive Reverse Voltage	V_{RRM}	100	V
Continuous Forward Current	I _F	250	mA
Peak Repetitive Forward Current	I _{FRM}	250	mA
Peak Forward Surge Current, tp=1.0µs	I _{FSM}	4.0	Α
Peak Forward Surge Current, tp=1.0s	I _{FSM}	1.0	Α
Power Dissipation	P_{D}	500	mW
Operating and Storage Junction Temperature	T _J , T _{stg}	-65 to +200	°C
Thermal Resistance	$\Theta_{\sf JA}$	350	°C/W


ELECTRICAL CHARACTERISTICS: (T_A=25°C unless otherwise noted) SYMBOL TEST CONDITIONS MIN **TYP** MAX UNITS 25 **V_R=20V** nΑ I_R $V_R = 75V$ 5.0 μΑ I_R BV_R I_R=100μA 100 V V_{F} I_E=10mA 1.0 V V_R=0, f=1 MHz 4.0 C_{T} pF $I_R = I_F = 10 \text{mA}$, $R_I = 100 \Omega$, t_{rr} Rec. to 1.0mA 4.0 5.0 ns

CLL914

SURFACE MOUNT HIGH SPEED SILICON SWITCHING DIODE



SOD-80 CASE - MECHANICAL OUTLINE



MARKING: CATHODE BAND

DIMENSIONS						
	INCHES		MILLIMETERS			
SYMBOL	MIN	MAX	MIN	MAX		
Α	0.130	0.146	3.30	3.71		
В	0.014		0.35			
C (DIA)	0.049	0.067	1.25	1.70		

SOD-80 (REV:R2)

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- · Inventory bonding
- · Consolidated shipping options

- · Custom bar coding for shipments
- · Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free guick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- · Custom electrical curves
- · Environmental regulation compliance
- · Customer specific screening
- · Up-screening capabilities

- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- · Application and design sample kits
- · Custom product and package development

REQUESTING PRODUCT PLATING

- 1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
- 2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp. 145 Adams Avenue Hauppauge, NY 11788 USA

Main Tel: (631) 435-1110 Main Fax: (631) 435-1824

Support Team Fax: (631) 435-3388

www.centralsemi.com

Worldwide Field Representatives: www.centralsemi.com/wwreps

Worldwide Distributors:

www.centralsemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centralsemi.com/terms

www.centralsemi.com (001)