High Current Composite Inductor - PA5175.XXXNLT and PM5175.XXXNLT







- *Height:* 5.0mm Max
- *Footprint:* 5.7mm x 5.5mm Max
- Current Rating: up to 7.2Arms
- Inductance Range: 5.6uH to 10uH
- Ø High current, low DCR, and high efficiency
- @ Rated Voltage between Terminals: 60V
- Minimized acoustic noise and minimized leakage flux noise
- Available in Commercial (PA5175) and Automotive (PM5175) grades


| Electrical Specifications @ 25°C, Operating Temperature Range –55°C to 155°C | | | | | | | | |
|--|-------------------------|--------------|--------------------|---------------|------|---|------------------|--|
| Part Number | | © Inductance | Rated ³ | DC Resistance | | Saturation Current ² (25°C) | K Factor | |
| Commerical | Automotive ⁶ | 100KHz, 0.1V | Current | TYP. | MAX. | TYP. | for Core Loss | |
| | | uH±20% | Α | m Ω | mΩ | A | | |
| PA5175.562NLT | PM5175.562NLT | 5.6 | 7.2 | 22.0 | 24.2 | 7.2 | 54.4 | |
| PA5175.682NLT | PM5175.682NLT | 6.8 | 6.4 | 26.0 | 28.6 | 6.6 | 47.9 | |
| PA5175.822NLT | PM5175.822NLT | 8.2 | 6.1 | 29.5 | 32.5 | 6.1 | 42.2 | |
| PA5175.103NLT | PM5175.103NLT | 10 | 5.0 | 39.0 | 43.0 | 5.4 | 42.2 | |

Notes:

- 1. Actual temperature of the component during system operation (ambient plus temperature rise) must be within the standard operating range.
- 2. The saturation current is the current at which the initial inductance is guaranteed to drop by no more than 40%. The typical inductance at a specified current can be found on the typical performance curves.
- 3. The rated current is the DC current required to raise the component temperature by approximately 40 ° C. Take note that the components' performanc varies depending on the system condition. It is suggested that the component be tested at the system level, to verify the temperature rise of the component during system operation.
- 4. The part temperature (ambient+temp rise) should not exceed 155 °C under worst case operating conditions. Circuit design, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.
- The PMxxxx.XXXNLT part numbers are AEC-Q200 and IATF16949 certified. The inductance and mechanical dimensions are 100% tested in production but do not necessarily meet a product capability index (Cpk) >1.33 and therefore may not strictly conform to PPAP.
- 6. Special Characteristics \bigcirc


High Current Composite Inductor - PA5175.XXXNLT and PM5175.XXXNLT





| Series | А | В | C | D | E | F | L | G | H |
|---------------|---------|---------|---------|---------|---------|----------|-----------|-----------|-----------|
| PA5175/PM5175 | 5.5±0.2 | 5.3±0.2 | 4.8±0.2 | 4.3±0.3 | 1.1±0.2 | 2.3±0.25 | 4.5 (REF) | 2.0 (REF) | 4.7 (REF) |

All Dimensions in mm.





| SURFACE MOUNTING TYPE, REEL/TAPE LIST | | | | | | | | |
|---------------------------------------|----------|---------|----------------|-----|----------------|----------|--|--|
| | REEL SIZ | ZE (mm) | TA | QTY | | | | |
| | A | G | P ₁ | W | K ₀ | PCS/REEL | | |
| PA5175/PM5175 | Ø330 | 16.4 | 8 | 16 | 5.3 | 1500 | | |


High Current Composite Inductor - PA5175.XXXNLT and PM5175.XXXNLT




Typical Performance Curves










P862. C (05/21)

High Current Composite Inductor - PA5175.XXXNLT and PM5175.XXXNLT



For More Information:

Americas - prodinfo_power@pulseelectronics.com | Europe - power-apps-europe@pulseelectronics.com | Asia - power-apps-asia@pulseelectronics.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2021. Pulse Electronics, Inc. All rights reserved.

4

PulseElectronics.com

P862. C (05/21)

