
3225 Crystal Clock Oscillator 3225XO Series

Frequency Range: 1.00MHz to 156.25MHz / 32.768KHz

Model C8

4 PADS 3.2 x 2.5






Features:

- High reliability & low cost unit
- Tight stability & extended temperature available
- Lead-free type
- For automotive applications, please contact our sales representatives

Standard Specifications

Item	Value
Frequency Range	1.00MHz to 156.25MHz / 32.768KHz
Frequency Stability	±50ppm (or specify)
Operating Temperature Range	-20°C to +70°C (or specify)
Operable Temperature Range	-40°C to +85°C
Operating Voltage	1.8V / 3.3V / 5.0V ±10%
Output Type	HCMOS
Output Load	15pF Max.
Current Consumption (Max)	1.8V: 3.3V 5.0V 1-16MHz: 5mA 1-16MHz: 7mA 1-16MHz: 15mA 17-80MHz: 12mA 17-80MHz: 20mA 17-60MHz: 35mA 81-156.25MHz: 20mA 81-156.25MHz: 20mA 32.768KHz: 0.2mA 32.768KHz: 0.2mA
Output Symmetry	HCMOS: 40~60%(at 50%V _{DD}); 45~55% is available
"High" Output Voltage	HCMOS: 90%V _{DD} Min.
"Low" Output Voltage	HCMOS: 10%V _{DD} Max.
Rise and Fall Time	1.8V / 3.3V 5.0V
	1-156.25MHz: 7ns Max. 1-60MHz: 10ns Max. 32.768KHz: 30ns Max.
Tri-State	Yes

Dimension



Custom specification is welcome. Please contact our sales representative for further details.

If the crystal is intended for applications which have direct impact on human life and properties, and require a high degree of reliability and safety concerns, customers must provide full information such as but not limit to

← α κ Ver 1.1

