


# 0136-20XX

PCB Terminal Blocks > PCB Terminal Blocks

Date:2022-06-09Version:V1





The web catalog is for reference only. Dinkle remains the right of product modification and engineering change of the design.

The final product is made according to engineering drawing.

### **Product Description**

Pitch: 3.50 mm, 300V, 6A

#### General information


Short description	PCB Terminal Blocks, Push-in Design
Category	PCB Terminal Blocks
Pitch (mm)	3.5
Color	Grey (default)
Connection method	Push in design
Type of locking	Without
Soldering method	Wave soldering
Length (mm)	3.50*(P-1)+5.0
Width (mm)	12
Height (mm)	13
Pin demensions (Thickness x Width)(mm)	0.4x0.75
PCB hole diameter (mm)	1
Number of positions	02P~24P
Level	Single level


#### Material information



Insulation material	PA
Insulation material group	I
Flame retardant rating , compliant with UL94	V0
Insulation resistance	□500MΩ at DC 500V
Conductor material	COPPER ALLOY
Plating of conductor surface	Tin PLATED
Connection data-IEC	
Rated voltage (V)	400
Rated current (A)	8
Rated voltage (II/2)(V)	630
Rated voltage (III/2) (V)	400
Rated voltage (III/3)(V)	250
Rated impulse voltage (II/2)(KV)	4
Rated impulse voltage (III/2)(KV)	4
Rated impulse voltage (III/3)(KV)	4
Conductor cross section solid. min (mm²)	0.2
Conductor cross section solid.max (mm²)	0.75
Conductor cross section stranded. min (mm²)	0.5
Conductor cross section stranded. max (mm²)	0.75
Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)	0.25
Conductor cross section flexible, with max ferrule without plastic sleeve (mm²)	0.75
Conductor cross section flexible, with min ferrule with plastic sleeve (mm²)	0.25
Conductor cross section flexible, with max ferrule with plastic sleeve (mm²)	0.5
Slotted screwdriver size (Blade thickness x Width)(mm)	0.4x2.5
Stripping Length (mm)	8~9
Connection data-UL	
Rated voltage (UL/CUL Group B)(V)	300
Rated current (UL/CUL Group B)(A)	6
Rated voltage (UL/CUL Group D)(V)	300
Rated current (UL/CUL Group D)(A)	6
Min. solid wire connection (AWG) acc. to UL/CUL	28

Drawings	
Rated current (A)	8
Rated voltage (V)	250
Wire Range (mm²)	0.2~0.75
VDE Approval	
Rated current (Group D)(A)	6
Rated voltage (Group D)(V)	300
Wire Ranget (Group D)(AWG)	28~16(SOL)
Rated current (Group B)(A)	6
Rated voltage (Group B)(V)	300
Wire Range (Group B)(AWG)	28~16(SOL)
CUL Recognized	
Rated current (Group D)(A)	6
Rated voltage (Group D)(V)	300
Wire Range (Group D)(AWG)	28~16(SOL)
Rated current (Group B)(A)	6
Rated voltage (Group B)(V)	300
Wire Range (Group B)(AWG)	28~16(SOL)
JL Recognized	
Operating temperature. min (°C)	-40
Operating temperature. max (°C)	120
Finger protection (YES or NO)	YES
Environment & Safety	
Max. stranded wire connection AWG acc. to UL/CUL	16
Min. stranded wire connection AWG acc. to UL/CUL	28
Max. solid wire connection AWG acc. to UL/CUL	16





## Approvals







