





APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-	7741	RELEASED	04/24/07	
A		REDRAWN	4/13/09	



RECOMMENDED PCB LAYOUT



**SPECIFICATIONS:**

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 800 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.

Positions: 2 thru 15  
 A = No. of Spaces x .098 [2.50]  
 B = No. of Positions x .098 [2.50] + .098 [2.50]

UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE INCHES [MM]  
 TOLERANCES: EXCEPT AS NOTED  
 INCHES

	HOLES	HOLE
.X	± .10	± .10
.XX	± .020	± .015
.XXX	± .015	± .010
.XXX	± .015	± .010

APPROVALS

DATE	DATE
04/24/07	

DRAWN BW

CHECKED

APPROVED

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: 2.5mm WAFER, RIGHT ANGLE 2P TO 15P

SIZE	PART NO.	REV.
X	25SH-C-XX-TR	A

REF.	SCALE:	SHEET	1 OF 1
S00016T	NIS		

