

NOTE:
 USE BUBBLE SHEETS INSIDE MASTER CARTON AT ENDS
 TO PROTECT TUBE CARTONS.
 BUBBLE SHEET P/N: 663345
 CUT THE BUBBLE SHEET INTO HALF.
 FOLD IN HALF AND PUT AT THE BOTH END OF CARTON.

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SCALE		CURRENT REV DESC: ADD TIN PLATE OPTION		molex		
	DIMENSION UNITS		SCALE		OPTION				
▽ = 0	mm	NTS		EC NO: 601113		PACKAGING SPECIFICATION 2MM PITCH BMI HEADER MILLIGRID			
▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DRWN: RMV02 2018/07/03					
▽ = 0	MM		INCH		CHK'D: GJEEVANSURES 2018/07/09		PACKAGING DESIGN DRAWING		
▽ = 0	4 PLACES ±		±		APPR: ISHWARG 2018/07/17				
▽ = 0	3 PLACES ±		±		INITIAL REVISION:		DOCUMENT NUMBER		
▽ = 0	2 PLACES ±		±		DRWN: GMENARLY 2014/07/03		DOC TYPE		
▽ = 0	1 PLACE ±		±		APPR: KHLIM 2014/08/27		DOC PART		
▽ = 0	0 PLACES ±		±		MATERIAL NUMBER		REVISION		
▽ = 0	ANGULAR TOL ± °		°		PK-151013-0001		PDD 001 A2		
▽ = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SHEET NUMBER		
▽ = 0			A3-SIZE		SERIES		CUSTOMER		
				151013		GENERAL MARKET		1 OF 2	

TUBE P/N	ASSEMBLY PART NUMBER	CKT SIZE	QUANTITY /TUBE	TUBE/ POPULATED CARTON	POPULATED CARTON/ MASTER CARTON	QUANTITY/ CARTON
151000-3004	151013-XX04	4	47	20	2	1880
	151013-XX06	6	40			1600
	151013-XX08	8	35			1400
	151013-XX10	10	30			1200
	151013-XX12	12	27			1080
	151013-XX14	14	25			1000
	151013-XX16	16	22			880
	151013-XX18	18	21			840
	151013-XX20	20	19			760

PART NUMBER LEGEND

151013-X X XX

CIRCUIT SIZE



PIN LENGTHS:

- 0: 2.60 mm
- 1: 4.00 mm
- 2: 3.00 mm
- 3: 3.50 mm
- 4: 4.50 mm
- 5: 2.10 mm

PLATING OPTIONS:

- 2: 0.76µm MIN. GOLD ON CONTACT, 1.27µm MATTE TIN ON SOLDERTAIL OVER 1.27µm MIN. NICKEL UNDERPLATE OVERALL
- 3: 0.38 µm MIN. GOLD ON CONTACT, 1.27 µm MATTE TIN ON SOLDERTAIL OVER 1.27 µm MIN. NICKEL UNDERPLATE OVERALL
- 4: 0.05 µm MIN. GOLD FLASH ON CONTACT, 1.27 µm MATTE TIN ON SOLDERTAIL OVER 1.27 µm MIN. NICKEL UNDERPLATE OVERALL
- 5: 2.50 µm MIN. MATTE TIN ON CONTACT, 1.27 µm MATTE TIN ON SOLDERTAIL OVER 1.27 µm MIN. NICKEL UNDERPLATE OVERALL

A2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
SYMBOLS	DIMENSION UNITS	SCALE	CURRENT REV DESC: ADD TIN PLATE OPTION								
	mm	NTS	 PACKAGING SPECIFICATION 2MM PITCH BMI HEADER MILLIGRID								
GENERAL TOLERANCES (UNLESS SPECIFIED)		MM								INCH	EC NO: 601113 DRWN: RMV02 2018/07/03 CHK'D: GJEEVANSURES 2018/07/09 APPR: ISHWARG 2018/07/17
▽ = 0	4 PLACES ±	±	PACKAGING DESIGN DRAWING								
▽ = 0	3 PLACES ±	±	INITIAL REVISION:								
▽ = 0	2 PLACES ±	±	DRWN: GMENARLY 2014/07/03								
▽ = 0	1 PLACE ±	±	APPR: KHLIM 2014/08/27								
□ = 0	0 PLACES ±	±	ANGULAR TOL ± °		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
■ = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				A3-SIZE	151013	SEE TABLE	GENERAL MARKET	2 OF 2		
▽ = 0							DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
						PK-151013-0001		PDD	001	A2	

DOCUMENT STATUS	P1	RELEASE DATE	2018/07/17	00:10:17
-----------------	----	--------------	------------	----------