

COMPLEMENTARY PAIR ENHANCEMENT MODE MOSFET

Product Summary

Device	BV _{DSS}	R _{DS(on)} Max	I _D Max T _A = +25°C	
		0.99Ω @ $V_{GS} = 4.5V$	500mA	
Q1	20V	1.2Ω @ $V_{GS} = 2.5V$	460mA	
QI	200	1.8Ω @ V _{GS} = 1.8V	375mA	
		$2.4\Omega @ V_{GS} = 1.5V$	320mA	
		1.9Ω @ V _{GS} = -4.5V	-360mA	
Q2	-20V	2.4Ω @ V _{GS} = -2.5V	-320mA	
Q2	-20V	3.4Ω @ V _{GS} = -1.8V	-270mA	
		5Ω @ V _{GS} = -1.5V	-225mA	

Description

This MOSFET is designed to minimize the on-state resistance (R_{DS(on)}) yet maintain superior switching performance, making it ideal for high-efficiency power management applications.

Applications

- General-purpose interfacing switches
- Power management functions
- Analog switches

Features and Benefits

- Low On-Resistance
- Very Low Gate Threshold Voltage
 - N-Channel: 1.0V Maximum
 - P-Channel: -1.0V Maximum
- Low Input Capacitance
- Fast Switching Speed
- Ultra-Small Surface Mount Package 1mm × 1mm
- **ESD Protected Gate**
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/


Mechanical Data


- Package: SOT963
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections Indicator: See Diagram
- Terminals: Finish—Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 @3
- Weight: 0.027 grams (Approximate)






Top View





P-Channel



Pin-Out

D1

Equivalent Circuit


Ordering Information (Note 4, 5)

Part Number	Bookaga	Packing		
Fait Number	Package	Qty.	Carrier	
DMC2991UDJ-7	SOT963	10,000	Tape & Reel	
DMC2991UDJ-7B	SOT963	10,000	Tape & Reel	

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and I ead-free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.
- 5. The options -7 and -7B stand for different taping orientations.

Marking Information



E1= Product Type Marking Code



Maximum Ratings Q1 N-CHANNEL (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit		
Drain-Source Voltage			V _{DSS}	20	V	
Gate-Source Voltage	V _{GSS}	±8	V			
Continuous Drain Current (Note 6) V 4 5V	Steady State	T _A = +25°C	- I _D	500	mA	
Continuous Drain Current (Note 6) V _{GS} = 4.5V		T _A = +70°C		400	IIIA	
Maximum Continuous Body Diode Forward Curre	nt (Note 7)	Is	430	mA		
Pulsed Drain Current (Note 7)		I _{DM}	1.8	А		

Maximum Ratings Q2 P-CHANNEL (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit		
Drain-Source Voltage			V_{DSS}	-20	V	
Gate-Source Voltage	V _{GSS}	±8	V			
Continuous Drain Current (Note C) // 4.51/	Steady State	T _A = +25°C	- I _D	-360	mA	
Continuous Drain Current (Note 6) V _{GS} = -4.5V		T _A = +70°C		-290	IIIA	
Maximum Continuous Body Diode Forward Currer	t (Note 7)	Is	-360	mA		
Pulsed Drain Current (Note 7)		I _{DM}	-1.1	Α		

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Total Power Dissipation (Note 6)		P_D	0.38	W
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	$R_{\theta JA}$	329	°C/W
Operating and Storage Temperature Range	T_{J} , T_{STG}	-55 to +150	°C	

Notes:

^{6.} Device mounted on FR-4 PCB, with minimum recommended pad layout.
7. Device mounted on minimum recommended pad layout test board, 10µs pulse duty cycle = 1%.



Electrical Characteristics Q1 N-CHANNEL (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 8)						
Drain-Source Breakdown Voltage	BV _{DSS}	20	_	_	V	$V_{GS} = 0V, I_D = 250\mu A$
Zero Gate Voltage Drain Current @T _C = +25°C	I _{DSS}		_	1	μA	$V_{DS} = 16V, V_{GS} = 0V$
Gate-Source Leakage	I _{GSS}	_	_	±10	μA	$V_{GS} = \pm 5V$, $V_{DS} = 0V$
ON CHARACTERISTICS (Note 8)						
Gate Threshold Voltage	V _{GS(th)}	0.4	_	1.0	V	$V_{DS} = V_{GS}$, $I_D = 250\mu A$
			0.36	0.99		$V_{GS} = 4.5V, I_D = 100mA$
Static Drain-Source On-Resistance	Dag.		0.46	1.2	Ω	$V_{GS} = 2.5V, I_D = 50mA$
Static Drain-Source On-Resistance	R _{DS(on)}	_	0.65	1.8		$V_{GS} = 1.8V, I_D = 20mA$
			0.92	2.4		$V_{GS} = 1.5V, I_D = 10mA$
Diode Forward Voltage	V_{SD}		0.6	1.0	V	$V_{GS} = 0V$, $I_S = 10mA$
DYNAMIC CHARACTERISTICS (Note 9)						
Input Capacitance	C _{iss}		21.5	_	pF	V 45V V 0V
Output Capacitance	Coss	_	4.9	_	pF	$V_{DS} = 15V, V_{GS} = 0V,$ f = 1.0MHz
Reverse Transfer Capacitance	C _{rss}		3.7	_	pF	1 = 1.01/11/12
Total Gate Charge	Qg		0.35	_	nC	45)/ 1/ 40)/
Gate-Source Charge	Q _{gs}	_	0.07	_	nC	$V_{GS} = 4.5V, V_{DS} = 10V,$ $I_{D} = 250 \text{mA}$
Gate-Drain Charge	Q _{gd}	_	0.08	_	nC	ID = 230IIIA
Turn-On Delay Time	t _{D(on)}	_	5.6	_	ns	
Turn-On Rise Time	t _R	_	4.9	_	ns	$V_{DD} = 10V, V_{GS} = 4.5V,$
Turn-Off Delay Time	t _{D(off)}	_	60.6	_	ns	$R_L = 47\Omega, R_g = 10\Omega,$ $I_D = 200 \text{mA}$
Turn-Off Fall Time	t _F	_	27.6	_	ns	ID = ZUUIIIA

Electrical Characteristics Q2 P-CHANNEL (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 8)						
Drain-Source Breakdown Voltage	BV _{DSS}	-20		_	V	$V_{GS} = 0V, I_D = -250\mu A$
Zero Gate Voltage Drain Current @T _C = +25°C	I _{DSS}	_	_	-1	μA	$V_{DS} = -16V, V_{GS} = 0V$
Gate-Source Leakage	I _{GSS}	_	_	±10	μΑ	$V_{GS} = \pm 5V$, $V_{DS} = 0V$
ON CHARACTERISTICS (Note 8)						
Gate Threshold Voltage	$V_{GS(th)}$	-0.4	1	-1.0	V	$V_{DS} = V_{GS}, I_{D} = -250 \mu A$
			1.0	1.9		$V_{GS} = -4.5V, I_D = -100mA$
Static Drain-Source On-Resistance	Б	_	1.25	2.4	Ω	$V_{GS} = -2.5V, I_{D} = -50mA$
Static Dialii-Source Off-Resistance	R _{DS(on)}	_	1.44	3.4		$V_{GS} = -1.8V, I_D = -20mA$
		_	1.8	5		$V_{GS} = -1.5V, I_D = -10mA$
Diode Forward Voltage	V _{SD}	_	-0.5	-1.1	V	$V_{GS} = 0V, I_{S} = -10mA$
DYNAMIC CHARACTERISTICS (Note 9)						
Input Capacitance	C _{iss}	1	17	1	pF	101/11/101/
Output Capacitance	Coss	_	4.1	_	pF	$V_{DS} = -16V, V_{GS} = 0V,$ f = 1.0MHz
Reverse Transfer Capacitance	C _{rss}	_	2.7	_	pF	1 = 1.000112
Total Gate Charge	Qg	_	0.3	_	nC	15///
Gate-Source Charge	Q_{gs}	_	0.04	_	nC	$V_{GS} = -4.5V, V_{DS} = -10V,$ $I_{D} = -250 \text{mA}$
Gate-Drain Charge	Q_{gd}	_	0.1	_	nC	ID = -250IIIA
Turn-On Delay Time	t _{D(on)}	_	7.3	_	ns	
Turn-On Rise Time	t _R	_	20.7	_	ns	$V_{DD} = -15V, V_{GS} = -4.5V,$
Turn-Off Delay Time	t _{D(off)}	_	185	_	ns	$R_g = 2\Omega$, $I_D = -200 \text{mA}$
Turn-Off Fall Time	t _F	_	97	_	ns	1

Notes: 8. Short duration pulse test used to minimize self-heating effect.

^{9.} Guaranteed by design. Not subject to product testing.



Typical Characteristics - N-CHANNEL




Figure 6. On-Resistance Variation with Junction Temperature

I_D, DRAIN CURRENT (A)

Figure 5. Typical On-Resistance vs. Drain Current and Junction Temperature



Typical Characteristics - N-CHANNEL (continued)




Figure 7. On-Resistance Variation with Junction Temperature




Figure 9. Diode Forward Voltage vs. Current




Figure 11. Gate Charge




Figure 8. Gate Threshold Variation vs. Junction Temperature






Figure 10. Typical Junction Capacitance





Typical Characteristics - P-CHANNEL






Figure 15. Typical On-Resistance vs. Drain Current and Gate Voltage




Figure 17. Typical On-Resistance vs. Drain Current and Junction Temperature




Figure 14. Typical Transfer Characteristic




Figure 16. Typical Transfer Characteristic




Figure 18. On-Resistance Variation with Junction Temperature



Typical Characteristics - P-CHANNEL (continued)




Figure 19. On-Resistance Variation with Junction Temperature




Figure 21. Diode Forward Voltage vs. Current




Figure 23. Gate Charge




Figure 20. Gate Threshold Variation vs. Junction Temperature





Figure 22. Typical Junction Capacitance









Figure 25. Transient Thermal Resistance



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT963




	SOT963						
Dim	Min	Max	Тур				
Α	0.40	0.50	0.45				
A1	0.00	0.05					
b	0.10	0.20	0.15				
С	0.120	0.180	0.150				
D	0.95	1.05	1.00				
Е	0.95	1.05	1.00				
E1	0.75	0.85	0.80				
е			0.35				
e1			0.70				
L1	0.05	0.15	0.10				
All	Dimens	All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT963



Dimensions	Value
Dimensions	(in mm)
С	0.350
Х	0.200
Y	0.200
Y1	1 100



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

DIODES is a trademark of Diodes Incorporated in the United States and other countries. The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. © 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com