

DIALIGHT PART NUMBER	LED COLOR	DIM "A"	DIM "B"	DIM "C"	DIM "D"	DIM "E"	OPERATING CHARACTERISTICS AT 25°C AMBIENT											
							LUMINOUS INTENSITY TEST CONDITION			FORWARD VOLTAGE / CURRENT TEST COND		FORWARD VOLTAGE (V)		FORWARD CURRENT (mA)		REVERSE CURRENT (mA)	PEAK WAVELENGTH (nm)	VIEWING ANGLE (DEG)
							MIN	TYP	MAX	TYP	MAX	TYP	MAX	TYP	MAX	MAX	TYP	TYP
551-0207-804F	GREEN TINTED DIFFUSED	.095	.118±.010	.115	.016 x .018	.040	If = 10mA	5.6	12.6	29	If = 10mA	2.1	2.6	—	—	100	565	60
551-0207-815F	GREEN TINTED DIFFUSED	.095	.118±.010	.110	.016 x .018	.040	If = 10mA	5.6	12.6	29	If = 10mA	2.1	2.6	—	—	100	565	60
551-0207-818F	GREEN TINTED DIFFUSED	.095	.118±.010	.177	.016 x .018	.040	If = 10mA	5.6	12.6	29	If = 10mA	2.1	2.6	—	—	100	565	60
551-0307-803F	YELLOW TINTED DIFFUSED	.095	.118±.010	.115	.016 x .018	.040	If = 10mA	3.7	8.7	30	If = 10mA	2.1	2.6	—	—	100	585	60
551-0307-807F	AlInGaP YELLOW WATER CLEAR	.095	.115±.010	UNTRIMMED	.018 SQ.	.040	If = 20mA	3.5	200	—	If = 20mA	1.9	2.4	—	—	100	592	45
551-0307-809F	YELLOW TINTED DIFFUSED	.095	.118±.010	.110	.016 x .018	.040	If = 10mA	3.7	8.7	30	If = 10mA	2.1	2.6	—	—	100	585	60
551-0307-812F	YELLOW TINTED DIFFUSED	.095	.118±.010	.210	.016 x .018	.040	If = 10mA	3.7	8.7	30	If = 10mA	2.1	2.6	—	—	100	585	60
551-0407-803F	RED TINTED DIFFUSED	.095	.118±.010	.115	.016 x .018	.040	If = 10mA	2.5	8.7	18	If = 10mA	2.0	2.6	—	—	100	635	60
551-0407-818F	RED TINTED DIFFUSED	.095	.118±.010	.110	.016 x .018	.040	If = 10mA	2.5	8.7	18	If = 10mA	2.0	2.6	—	—	100	635	60
551-0507-801F	RED TINTED DIFFUSED; 5V INT RES	.095	.118±.010	.115	.018 x .016	.040	Vf = 5V	8.7	29	—	Vf = 5V	—	—	10	20	100	635	60
551-0507-806F	RED TINTED DIFFUSED; 5V INT RES	.095	.118±.010	.110	.018 x .016	.040	Vf = 5V	8.7	29	—	Vf = 5V	—	—	10	20	100	635	60
551-0607-801F	GREEN TINTED DIFFUSED; 5V INT RES	.095	.118±.010	.110	.018 x .016	.040	Vf = 5V	5.6	19	—	Vf = 5V	—	—	10	20	100	565	60
* 551-1107-801F	RED TINTED DIFFUSED; 2mA LC	.095	.118±.010	.145	.018 x .016	.040	If = 2mA	1.0	1.6	—	If = 2mA	1.7	2.2	—	—	10	635	60
551-1107-811F	RED TINTED DIFFUSED; 2mA LC	.095	.118±.010	.110	.018 x .016	.040	If = 2mA	1.0	1.6	—	If = 2mA	1.7	2.2	—	—	10	635	60
* 551-1207-801F	YELLOW TINTED DIFFUSED; 2mA LC	.095	.118±.010	.145	.018 x .016	.040	If = 2mA	1.0	1.6	—	If = 2mA	1.8	2.7	—	—	10	585	60
551-1207-809F	YELLOW TINTED DIFFUSED; 2mA LC	.095	.118±.010	.110	.018 x .016	.040	If = 2mA	1.0	1.6	—	If = 2mA	1.8	2.7	—	—	10	585	60
* 551-1307-801F	GREEN TINTED DIFFUSED; 2mA LC	.095	.118±.010	.145	.018 x .016	.040	If = 2mA	1.0	1.6	—	If = 2mA	1.9	2.2	—	—	10	565	60
551-1307-811F	GREEN TINTED DIFFUSED; 2mA LC	.095	.118±.010	.110	.018 x .016	.040	If = 2mA	1.0	1.6	—	If = 2mA	1.9	2.2	—	—	10	565	60
551-1307-812F	GREEN TINTED DIFFUSED; 2mA LC	.095	.115±.010	.145	.018 SQ.	.040	If = 2mA	1.0	2.1	—	If = 2mA	1.8	2.2	—	—	50	565	50
551-3007-803F	R/G BI-COLOR, WHITE DIFFUSED	.095	.118±.010	.110	.020 SQ.	.043	If = 10mA	2.5	4.7	—	If = 20mA	2.0	2.8	—	—	100	635	60
								3.7	10	—		2.1	2.8	—	—	100	565	60
551-4207-803F	InGaN GREEN WATER CLEAR	.101	.110±.005	.145	.020 SQ.	.043	If = 10mA	280	480	710	If = 10mA	3.0	3.7	—	—	10	523	30


REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
A	—	NEW RELEASE	KLJ	—	—	—
B	—	UPDATED DIM A,B, D & E FOR P/N'S 551-0207/0307/0407-8XXF. ALSO UPDATED LED SPECS	BP	—	NO	8-22-16

**RoHS COMPLIANT 551-XX07-8XXF**

Part Numbers with the "F" suffix ending are RoHS Compliant. For example: 551-0207-818F  
Packaging is marked with "RoHS Compliant" label or equivalent markings. Parts can be wave soldered, dip soldered or hand soldered using typical lead-free soldering process with max 260°C temp. for 5 sec.

DIALIGHT PART NUMBER	ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT								
	POWER DISSIPATION (mW)	CONT. FWD CURRENT (mA)	DC FORWARD VOLTAGE (V)	PEAK FWD CURRENT (mA)	LINEAR DERATION	REVERSE VOLTAGE (V)	SOLDERING TEMPERATURE FOR 5 SEC.	OPERATING TEMPERATURE	STORAGE TEMPERATURE
551-0207-804F	120	30	—	90	0.4 mA/°C FROM 50°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
551-0207-815F	120	30	—	90	0.4 mA/°C FROM 50°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
551-0207-818F	120	30	—	90	0.4 mA/°C FROM 50°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
551-0307-803F	60	20	—	60	0.25 mA/°C FROM 50°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
551-0307-807F	103	50	—	500	0.84 mA/°C FROM 50°C	5	260 °C	-40°C /+100°C	-40°C /+100°C
551-0307-809F	60	20	—	60	0.25 mA/°C FROM 50°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
551-0307-812F	60	20	—	60	0.25 mA/°C FROM 50°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
551-0407-803F	100	30	—	90	0.4 mA/°C FROM 50°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
551-0407-818F	100	30	—	90	0.4 mA/°C FROM 50°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
551-0507-801F	—	—	7.5	—	0.086 V/°C FROM 50°C	5	260 °C	-40°C /+85°C	-55°C /+100°C
551-0507-806F	—	—	7.5	—	0.086 V/°C FROM 50°C	5	260 °C	-40°C /+85°C	-55°C /+100°C
551-0607-801F	—	—	7.5	—	0.086 V/°C FROM 50°C	5	260 °C	-40°C /+85°C	-55°C /+100°C
* 551-1107-801F	20	7	—	500	0.7 mA/°C FROM 90°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
551-1107-811F	20	7	—	500	0.7 mA/°C FROM 90°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
* 551-1207-801F	20	7	—	500	0.7 mA/°C FROM 90°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
551-1207-809F	20	7	—	500	0.7 mA/°C FROM 90°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
* 551-1307-801F	20	7	—	500	0.7 mA/°C FROM 90°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
551-1307-811F	20	7	—	500	0.7 mA/°C FROM 90°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
551-1307-812F	24	7	—	500	1.0 mA/°C FROM 92°C	5	260 °C	-20°C /+100°C	-40°C /+100°C
551-3007-803F	100	30	—	120	0.4 mA/°C FROM 50°C	5	260 °C	-55°C /+100°C	-55°C /+100°C
551-4207-803F	80	20	—	250	0.57 mA/°C FROM 65°C	5	260 °C	-55°C /+100°C	-55°C /+100°C



\* PACKAGE 100 PCS/TUBE WITH TWO [2] END PLUGS FOR THESE P/N'S ONLY



**RECOMMENDED P.C.B. HOLE PATTERN**

**NOTES:**

- LED LEAD DIMENSIONS SHOWN ARE MEASURED AT HOUSING EXIT.
- LEADS TO FIT INTO HOLES SPACED AS PER PATTERN.
- PIN NUMBERS FOR REFERENCE ONLY, DESIGNATION NON-EXISTENT ON PART.
- DIALIGHT PART NUMBERS: 551-XX07-8XXF.
- THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS). MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING, AND STORAGE IN ACCORDANCE WITH IPC-A-610.



**ATTENTION:**  
OBSERVE PRECAUTIONS FOR HANDLING ELECTROSTATIC SENSITIVE DEVICES

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.		
SCALE: DRAWING SCALE	DRAWING NUMBER	REV
ALL DIM'S IN: INCHES (MM)	C-17721	B
TOLERANCES: UNLESS OTHERWISE SPECIFIED	TITLE	
FRACTIONS: ±1/64	3mm LED CBI .200" HIGH	
DECIMALS (.XX): ±.02	RoHS COMPLIANT	
DECIMALS (.XXX): ±.010	MATERIAL	
ANGLES: ±3°		
FINISH:		
FSCM 83330	Dialight	1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727
	SHEET 1 OF 1	FAMILY TABLE: