

2A, 50V - 1400V Standard Surface Mount Rectifier

FEATURES

- Glass passivated chip junction
- Ideal for automated placement
- Low forward voltage drop
- High surge current capability
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- Lighting application
- Converter

MECHANICAL DATA

- Case: DO-214AA (SMB)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.090g (approximately)

KEY PARAMETERS				
PARAMETER	VALUE	UNIT		
I _F	2	А		
V _{RRM}	50 - 1400	V		
I _{FSM}	50	А		
T _{J MAX}	150	°C		
Package	DO-214AA (SMB)			
Configuration	Single die			





DO-214AA (SMB)



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^{\circ}C$ unless otherwise noted)											
PARAMETER	SYMBOL	S2A	S2B	S2D	S2G	S2J	S2K	S2M	S2Q	S2V	UNIT
Marking code on the device		S2A	S2B	S2D	S2G	S2J	S2K	S2M	S2Q	S2V	
Repetitive peak reverse voltage	V _{RRM}	50	100	200	400	600	800	1000	1200	1400	V
Reverse voltage, total rms value	V _{R(RMS)}	35	70	140	280	420	560	700	840	980	V
Forward current	I _F	2				А					
Surge peak forward current, 8.3ms single half sine-wave superimposed on rated load	I _{FSM}	50				A					
Junction temperature	TJ	T _J - 55 to +150			°C						
Storage temperature	T _{STG}	- 55 to +150			°C						



THERMAL PERFORMANCE					
PARAMETER	SYMBOL	ТҮР	UNIT		
Junction-to-lead thermal resistance	$R_{\Theta JL}$	16	°C/W		
Junction-to-ambient thermal resistance	$R_{\Theta J A}$	53	°C/W		

ELECTRICAL SPECIFICATIONS (TA = 25°C unless otherwise noted)						
PARAMETER	CONDITIONS	SYMBOL	ТҮР	МАХ	UNIT	
Forward voltage ⁽¹⁾	I _F = 2A, T _J = 25°C	V _F	-	1.15	V	
Reverse current @ rated $V_R^{(2)}$	$T_J = 25^{\circ}C$		-	1	μA	
	T _J = 125°C	I _R	-	125	μA	
Junction capacitance	1MHz, V _R = 4.0V	CJ	30	-	pF	
Reverse recovery time	$I_F = 0.5A, I_R = 1.0A$	+	1500	-	ns	
	$I_{rr} = 0.25A$	t _{rr}				

Notes:

- 1. Pulse test with PW = 0.3ms
- 2. Pulse test with PW = 30ms

ORDERING INFORMATION				
ORDERING CODE ⁽¹⁾	PACKAGE	PACKING		
S2x	DO-214AA (SMB)	3,000 / Tape & Reel		

Notes:

1. "x" defines voltage from 50V(S2A) to 1400V(S2V)



CHARACTERISTICS CURVES

(T_A = 25°C unless otherwise noted)




Fig.1 Forward Current Derating Curve





Fig.2 Typical Junction Capacitance

REVERSE VOLTAGE (V)

Fig.3 Typical Reverse Characteristics

Fig.4 Typical Forward Characteristics





CHARACTERISTICS CURVES

(T_A = 25°C unless otherwise noted)






Fig.5 Maximum Non-Repetitive Forward Surge Current


Fig.6 Reverse Recovery Time Characteristic and Test Circuit Diagram









PACKAGE OUTLINE DIMENSIONS





DIM.	Unit	(mm)	Unit (inch)		
	Min.	Max.	Min.	Max.	
Α	1.95	2.65	0.077	0.104	
A1	0.05	0.20	0.002	0.008	
b	1.95	2.20	0.077	0.087	
с	0.15	0.31	0.006	0.012	
D	3.30	3.95	0.130	0.156	
E	5.10	5.60	0.201	0.220	
E1	4.05	4.60	0.159	0.181	
L	0.75	1.60	0.030	0.063	

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	2.30	0.091
В	2.50	0.098
С	4.30	0.169
D	1.80	0.071
E	6.80	0.268

MARKING DIAGRAM



G = Green Compound

YW = Date Code

F = Factory Code



Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.