



Recommended PCB Layout (Bottom View)

Part Number	Contact Area Plating Finish
K42X-C37S/S-A4N	Gold Flash (standard option)
K42X-C37S/S-A4N15	15u" Gold (15 option)
K42X-C37S/S-A4N30	30u" Gold (30 option)

Material and Finish

- Shell: Steel, Nickel plated
- Insulator: PBT thermoplastic with glass-fiber reinforcement, UL94V-0 rated
Color: Black
- Contact Material:
Socket - Phosphor Bronze
- Contact Plating Options:
Standard: gold flash on mating end, tin on termination end, nickel underplate on entire contact
15 Option: 15u" gold on mating end, tin on termination end, nickel underplate on entire contact
30 Option: 30u" gold on mating end, tin on termination end, nickel underplate on entire contact

Electrical Specifications

- Rated Current: 1.2A
- Rated Voltage: 30V RMS
- Insulation Resistance:
more than 1000 megohms at 500V DC
- Contact Resistance:
13 milliohms max.
- Dielectric Withstanding Voltage:
1000V for 1 minute
- Operating Temperature:
-55°C to +105°C



Tolerances
X.X ± 0.25
X.XX ± 0.15
Unless Stated Otherwise

REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A1	02/23/09	New Drawing	S. Vien	H. MA	S. Vien	02/23/09
A2	12/31/17	ECO #17-037	G. Serrato	C. Furumasa		
A3	03/25/19	ECO #19-020	H. MA	D. Shehan		
					UNITS	
					mm	

K42X-C37S/S-A4N

D-Sub, Dual Port, 37 Female/Female
0.750" Spacing, RoHS Compliant

