

ezPyro[™] SMD+ I²C Pyroelectric Extended Infrared Sensor for Gas Sensing

Introduction

The ezPyroTM SMD+ infrared detector range extends the ezPyro family to offer sensing at wavelengths above 5 μm, accessing a wider range of applications such as NDIR detection of anesthetic, refrigerant and exhaust gases. These thin film digital pyroelectric devices for gas detection and concentration measurement combine high quality sensors with a high level of configurable electronic integration in a small SMD package. High sensitivity combined with fast response times ensure rapid and accurate detection of target gases. These sensors integrate a digital, current mode read-out that enables lower IR-emitter duty cycles, thereby saving significantly on system level power consumption,



while maintaining high SNR. Programmable gain and filtering offer maximum flexibility in system design. Industry standard I²C communication enables plug-and-play connectivity to microcontrollers and allows easy tuning and calibration. ezPyro sensors are very stable over time ensuring a long and maintenance-free operational lifespan. Various optical filter options are available. These sensors can also be daisy-chained to allow synchronized sampling across devices.

Sensor Charac	teristics
Filter aperture	d = 1.65 mm
Element size	0.64 x 0.64 mm ²
SMD Package	5.65 x 3.7 x 1.75 mm
D* (typ.) 1	$2.5 \times 10^8 \text{ cm}\sqrt{\text{Hz}/\text{ W}}$
NEP (typ.) 1	2.7 x 10 ⁻¹⁰ W/√Hz
Time Constant	~10ms (10-20 Hz peak)
Field of View	~40°


Electrical Characteris	tics
Supply voltage	1.75 to 3.6 V
Supply current (typ.)	1 to 23 μA
Digital I/O	I ² C (FM+ compatible)
ADC	15bit ΔΣ ADC @1ksp
Operating Temperature	-40 to +85 °C
Storage Temperature	-40 to +110 °C
Sensor read-out	Current mode
Configurable	Gain / digital filtering / sampling rate / power modes

¹⁾ Measured without filter @ 500K, 10 Hz, room temperature

(Order Information				
	Part Number	Marking	Filter µm	Filter BW μm	Package Size
	AFBR-S6EPY32301R	Y32301	8.42	205	800 pcs on 7-in. tape and reel
	AFBR-S6EPY32271R	Y32271	9.50	400	800 pcs on 7-in. tape and reel



Package Information




Signal Filtering & Power Modes

Power Mode (base sample rate)	High	Pass	Filter –	Analog	j (Hz)	Fixed Analog Low Pass Filter (Hz)	Fixed Digital Low Pass Filter (Hz)	Digital Low Pass Filter (Hz)			Max ADC Sampling Rate (sps)	
Normal Power Mode	Off	1	2	4	8	600	250	180	90	45	22.5	1000
Low Power Mode	Off	0.17	0.33	0.66	1.3	100	42	30	15	7.5	3.75	166


	Mode	Description	Typical Current Consumption (1.8 V, room temperature)		
Power	Normal Power Mode	Normal power consumption, 1 kHz max. sample rate	22 μΑ		
consumption	Low Power Mode	Low power consumption, 166 Hz max. sample rate	3.5 μΑ		
	Normal Operation Mode	Sensor signal readout over I ² C	22 μΑ		
Operational state	Sleep Mode	Hardware interrupt on infrared trigger	21 μA (Normal), 3.5 μA (Low)		
	Power Down Mode	Sensor is disabled	1.1 μΑ		

Circuit Diagrams

Single Device Block Diagram




Three Devices with Synchronised Sampling





Infrared Frequency Characteristics




100

(ne)

(

Typical Frequency Response in Normal Power Mode

Typical Frequency Response in Low Power Mode



Typical Frequency Response at Different Gain Settings

Copyright © 2022 Broadcom. All Rights Reserved. The term "Broadcom" refers to Broadcom Inc. and/or its subsidiaries. For more information, go to www.broadcom.com . All trademarks, trade names, service marks, and logos referenced herein belong to their respective companies.
Broadcom reserves the right to make changes without further notice to any products or data herein to improve reliability, function, or design. Information furnished by Broadcom is believed to be accurate and reliable. However, Broadcom does not assume any liability arising out of the application or use of this information, nor the application or use of any product or circuit described herein, neither does it convey any license under its patent rights nor the rights of others. AFBR-S6EPYSMDP-GA-DS100