

### Features

- Halogen Free. "Green" Device (Note 1)
- High Surge Forward Current Capability
- Lead Free Finish/RoHS Compliant (Note 2) ("P"Suffix Designates Compliant. See Ordering Information)
- Epoxy Meets UL 94 V-0 Flammability Rating



## **Maximum Ratings**

- Operating Junction Temperature Range: -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- Typical Thermal Resistance: 68°C/W Junction to Ambient
- Typical Thermal Resistance: 15°C/W Junction to Lead


MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
DB201L	DB201L	50V	35V	50V
DB202L	DB202L	100V	70V	100V
DB203L	DB203L	200V	140V	200V
DB204L	DB204L	400V	280V	400V
DB205L	DB205L	600V	420V	600V
DB206L	DB206L	800V	560V	800V
DB207L	DB207L	1000V	700V	1000V

### Electrical Characteristics @ 25°C Unless Otherwise Specified

Average Forward Current	I <sub>F(AV)</sub>	2.0A	Tœ=40°C
Peak Forward Surge Current	I <sub>FSM</sub>	60A	8.3ms, Half Sine
Maximum Instantaneous Forward Voltage	V <sub>F</sub>	1.FV	I <sub>FM</sub> =2.0A; T <sub>J</sub> =25°C
Maximum DC Reverse Current At Rated DC Blocking Voltage	I <sub>R</sub>	10µA	TJ=25°C
I <sup>2</sup> t Rating For Fusing	l²t	15A <sup>2</sup> S	(1ms< t<8.3ms)TJ=25°C, Rating of Per Diode

Note: 1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

2. High Temperature Solder Exemption Applied, see EU Directive Annex 7a.





DIMENSIONS						
DIM	INCHES		MM		NOTE	
	MIN	MAX	MIN	MAX	NOTE	
Α	0.316	0.335	8.05	8.51		
В	0.245	0.255	6.20	6.50		
С	0.300	0.350	7.60	8.90		
D	0.150	0.185	3.81	4.69		
Е	0.093	0.096	2.35	2.45		
F	0.050	0.080	1.27	2.03		
G	0.018	0.023	0.46	0.56		
Н	0.195	0.205	5.00	5.20		








# **Curve Characteristics**
















## **Ordering Information**

Device	Packing	
Part Number-BP	Bulk:50pcs/Tube,2500pcs/Box,10Kpcs/Carton	

#### \*\*\*IMPORTANT NOTICE\*\*\*

*Micro Commercial Components Corp.* reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. *Micro Commercial Components Corp*. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp*. and all the companies whose products are represented on our website, harmless against all damages. *Micro Commercial Components Corp*. products are sold subject to the general terms and conditions of commercial sale, as published at

https://www.mccsemi.com/Home/TermsAndConditions.

### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

#### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources**. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.