



Recommended PCB Layout
(Bottom View)

Part Number	Contact Area Plating Finish
K42X-A15S/S-A4NJ	Gold Flash (standard)
K42X-A15S/S-A4NJ15	15u" Gold (15 option)
K42X-A15S/S-A4NJ30	30u" Gold (30 option)

Material and Finish

Shell: Steel, nickel plated
 Insulator: PBT thermoplastic with glass-fiber reinforcement, UL94V-0 rated
 Color: Black

Contact Material:
 Socket - Phosphor Bronze
 Contact Plating Options:
 Standard: gold flash on mating end, tin on termination end, nickel underplate on entire contact
 15 Option: 15u" gold on mating end, tin on termination end, nickel underplate on entire contact
 30 Option: 30u" gold on mating end, tin on termination end, nickel underplate on entire contact

Electrical Specifications

Rated Current: 1.2A
 Rated Voltage: 30V RMS
 Insulation Resistance: more than 1000 megohms at 500V DC
 Contact Resistance: 13 milliohms max.
 Dielectric Withstanding Voltage: 1000V for 1 minute
 Operating Temperature: -55°C to +105°C

RoHS COMPLIANT



Tolerances
X.X ± 0.25
X.XX ± 0.15
Unless Stated Otherwise

REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A1	11/09/09	New Drawing	S. Vien	H. MA	S. Vien	09/30/09
A2	12/31/17	ECO #17-037	J. Elbanna	C. Furumasa		
A3	03/11/19	ECO #19-020	H. MA	D. Shehan		
						UNITS
						mm

K42X-A15S/S-A4NJ

Stacked D-Sub, 15/15 Female, RoHS Compliant

0.750" Spacing, Boardlocks, JS

