

Features

- High Temperature Soldering Guaranteed:260°C/10 Second
- · Saves Space On Printed Circuit Board
- Halogen Free Available Upon Request By Adding Suffix "-HF"
- Epoxy Meets UL 94 V-0 Flammability Rating
- Moisture Sensitivity Level 1
- Lead Free Finish/RoHS Compliant (Note1) ("P"Suffix Designates Compliant. See Ordering Information)
- Teminals: Plated Leads Solderable Per MIL-STD-750, Method 2026

Maximum Ratings

- Operating Junction Temperature Range: -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- Typical Thermal Resistance(Note2): 134°C/W Junction to Ambient
- Typical Thermal Resistance(Note3): 134°C/W Junction to Ambient
- Typical Thermal Resistance(Note2): 20°C/W Junction to Lead


MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
MBL1S	BL1S	100V	70V	100V
MBL2S	BL2S	200V	140V	200V
MBL4S	BL4S	400V	280V	400V
MBL6S	BL6S	600V	420V	600V
MBL8S	BL8S	800V	480V	800V
MBL10S	BL10S	1000V	700V	1000V

Electrical Characteristics @ 25°C Unless Otherwise Specified


Average Forward Current	I _{F(AV)}	0.5A ⁽²⁾ 0.8A ⁽³⁾	See Fig.1
Peak Forward Surge Current	I _{FSM}	35A	8.3ms, Half Sine
Maximum Instantaneous Forward Voltage	V _F	1.0V	I _{FM} = 0.4A T _A = 25°C
Maximum DC Reverse Current at Rated DC Blocking Voltage	I _R	10μΑ	T _A = 25°C
Typical Junction Capacitance	Сл	13pF	Measured at 1.0MHz, V _R =4.0V
Rating For Fusing	l²t	5.1A ² S	t<8.3ms

- Note: 1. High Temperature Solder Exemption Applied, see EU Directive Annex Notes 7
 - 2. On glass epoxy P.C.B. mounted on 0.05 x 0.05"(1.3 x 1.3mm)pads
 - 3. On aluminum substrate P.C.B. with an area of 0.8" x 0.8"(20 x 20mm) mounted on 0.05 x 0.05"(1.3x 1.3mm) solder pad

0.5 Amp Single Phase Glass Passivated Bridge Rectifier 100 to 1000 Volts





DIMENSIONS					
DIM	INC	HES N		IM	NOTE
DIIVI	MIN	MAX	MIN	MAX	NOTE
Α	0.252	0.283	6.40	7.20	
В	0.087	0.102	2.20	2.60	
С	0.142	0.193	3.60	4.90	
D	0.177	0.200	4.55	5.10	
E	0.022	0.033	0.55	0.84	
F	0.045	0.063	1.15	1.60	
G	0.000	0.008	0.00	0.20	
Н	0.016	0.043	0.40	1.10	
J	0.004	0.016	0.10	0.35	






Curve Characteristics











Fig. 4 - Typical Reverse Leakage Characteristics





Ordering Information

	Device	Packing
Part Number-TP		Tape&Reel4Kpcs/Reel

Note: Adding "-HF" Suffix For Halogen Free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp**. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp**, and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp**, products are sold subject to the general terms and conditions of commercial sale, as published at

https://www.mccsemi.com/Home/TermsAndConditions.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.