

# 1A, 400V - 1000V Fast Recovery Rectifier

#### **FEATURES**

- AEC-Q101 qualified available
- Glass passivated chip junction
- High current capability, Low V<sub>F</sub>
- High reliability
- High surge current capability
- Low power loss, high efficiency
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

#### **APPLICATIONS**

- DC to DC converter
- Switching mode converters and inverters
- General purpose

#### **MECHANICAL DATA**

- Case: DO-204AL (DO-41)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Pure tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.330g (approximately)

KEY PARAMETERS				
PARAMETER	VALUE	UNIT		
I <sub>F</sub>	1	Α		
$V_{RRM}$	400 - 1000	V		
I <sub>FSM</sub>	30	Α		
$T_{JMAX}$	150	°C		
Package	DO-204AL (DO-41)			
Configuration	Single die			







ABSOLUTE MAXIMUM RATINGS (T <sub>A</sub> = 25°C unless otherwise noted)						
PARAMETER	SYMBOL	BA157G	BA158G	BA159G	UNIT	
Marking code on the device		BA157G	BA158G	BA159G		
Repetitive peak reverse voltage	$V_{RRM}$	400	600	1000	V	
Reverse voltage, total rms value	$V_{R(RMS)}$	280	420	700	V	
Forward current	I <sub>F</sub>	1		Α		
Surge peak forward current, 8.3ms single half sine wave superimposed on rated load	I <sub>FSM</sub>	30		А		
Junction temperature	T <sub>J</sub>	-55 to +150			°C	
Storage temperature	T <sub>STG</sub>	-55 to +150			°C	

Taiwan Semiconductor

THERMAL PERFORMANCE					
PARAMETER	SYMBOL	TYP	UNIT		
Junction-to-ambient thermal resistance	$R_{\Theta JA}$	60	°C/W		

ELECTRICAL SPECIFICATIONS (T <sub>A</sub> = 25°C unless otherwise noted)						
PARAMETER		CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage <sup>(1)</sup>		$I_F = 1A, T_J = 25^{\circ}C$	V <sub>F</sub>	-	1.2	V
Reverse current @ rated V <sub>R</sub> <sup>(2)</sup> Junction capacitance		T <sub>J</sub> = 25°C	1	-	5	μA
		T <sub>J</sub> = 125°C	l <sub>R</sub>	-	100	μA
		1MHz, $V_R = 4.0V$	CJ	15	-	pF
Reverse recovery time	BA157G BA158G	I <sub>F</sub> = 0.5A, I <sub>R</sub> = 1.0A,	t <sub>rr</sub>	-	150	ns
	BA159G	$I_{rr} = 0.25A$	-	250	ns	

#### Notes:

- 1. Pulse test with PW = 0.3ms
- 2. Pulse test with PW = 30ms

PRDERING INFORMATION				
ORDERING CODE <sup>(1)(2)</sup>	PACKAGE	PACKING		
BA15xG	DO-204AL (DO-41)	5,000 / Tape & Reel		
BA15xG A0G	DO-204AL (DO-41)	3,000 / Ammo box		
BA15xGH	DO-204AL (DO-41)	5,000 / Tape & Reel		
BA15xGHA0G	DO-204AL (DO-41)	3,000 / Ammo box		

#### Notes:

- 1. "x" defines voltage from 400V (BA157G) to 1000V (BA159G)
- 2. "H" means AEC-Q101 qualified



#### **CHARACTERISTICS CURVES**

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$ 

**Fig.1 Forward Current Derating Curve** 




Fig.3 Typical Reverse Characteristics





Fig.2 Typical Junction Capacitance

**Fig.4 Typical Forward Characteristics** 







Fig.5 Maximum Non-Repetitive Forward Surge Current



NUMBER OF CYCLES AT 60 Hz


3





### **CHARACTERISTICS CURVES**

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$ 

Fig.6 Reverse Recovery Time Characteristic and Test Circuit Diagram










## **PACKAGE OUTLINE DIMENSIONS**



DIM. Unit		(mm)	Unit (inch)		
Dilvi.	Min.	Max.	Min.	Max.	
Α	25.40	-	1.000	-	
В	4.20	5.20	0.165	0.205	
С	0.71	0.86	0.028	0.034	
D	2.00	2.70	0.079	0.106	

### **MARKING DIAGRAM**



= Marking Code P/N G = Green Compound

YWW = Date Code = Factory Code F





#### **Notice**

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.