

TMR2505

Z-axis TMR linear sensor

General Description


The TMR2505 linear sensor utilizes a unique push-pull Wheatstone bridge composed of four unshielded TMR sensor elements. The unique bridge design provides a high sensitivity differential output that is linearly proportional to a magnetic field applied perpendicular to the surface of the sensor package, and it provides superior temperature compensation of the output. The TMR2505 is available in the TO94(P/N TMR2505T),SSIP4(P/N TMR2505B), or SOT23-5(P/N TMR2505S) packages.

Features and Benefits

- Tunneling Magneto resistance (TMR) Technology
- High Sensitivity
- Large Dynamic Range
- Low Power Consumption
- Excellent Thermal Stability
- Very Low Hysteresis
- Compatible with wide Range of Supply Voltages

Applications


- Magnetic Field Sensing
- Current Sensors
- Motor and Fan Drivers
- Position and Displacement Sensors



TMR2505S, TMR2505B, TMR2505T


Transfer Curve

The following figure shows the response of the TMR2505 to an applied magnetic field in the range of ±2000 Oe and +/-200Oe when the TMR2505 is biased at 1V.



Pin Configuration

Note: Arrow indicates direction of applied field (N-S) that generates a positive output voltage.



Pin No.(TO94/SSIP4)	Pin No.(SOT23-5)	Pin Name	Pin Function	
1	4	GND	Ground	
2	5	Vout-	Analog Differential Output 1	
3	1	V_{DD}	Supply Voltage	
4	3	Vout+	Analog Differential Output 2	
-	2	NC	NC	

Absolute Maximum Ratings

Parameter	Symbol	Limit	Unit
Supply Voltage	V_{DD}	7	V
Reverse Supply Voltage	V_{RDD}	-7	V
Max Exposed Field	HE	4000	Oe ⁽¹⁾
ESD Voltage	V _{ESD}	4000	V
Operating Temperature	T _A	-55~150	°C
Storage Temperature	T _{stg}	-70 ~165	°C

Specification (V_{CC}=1.0V, T_A=25°C, Differential Output)


Parameter	Symbol	Conditions	Min	Тур	Max	Unit
Supply Voltage	V_{DD}	Operating		1	7	V
Supply Current	Icc	Output Open		0.625(2)		uA
Resistance(SOP8)	R			1.6(2,3)		Mohm
Sensitivity	SEN	Fit @ ±30 Oe		2.2		mV/V/Oe
Saturation Field	H _{sat}			±100		Oe
Non-Linearity	NONL	Fit @ ±30 Oe		1		%FS
Offset Voltage	Voffset		-10		10	mV/V
Hysteresis	Hys	Fit @ ±30 Oe			1	Oe
Temperature Coefficient of Resistance	TCR	H = 0 Oe		-1000		PPM/°C
Temperature Coefficient of Offset	TCO	-55°C~150°C		-0.02		mV/V/°C
Temperature Coefficient of Sensitivity	TCS	-55°C~150°C		245		PPM/°C


Notes:

- (1) 1 Oe (Oersted) = 1 Gauss in air = 0.1 millitesla = 79.8 A/m.
- (2) Icc= Vcc/ R.
- (3) Custom resistance may be available upon request.

Package Information


TO94 (P/N TMR2505T) package drawing:






Symbol	Dimensions In Millimeters		Dimensions In Inches		
	Min	Max	Min	Max	
Α	1.400	1.800	0.055	0.071	
A1	0.700	0.900	0.028	0.035	
A2	0.500	0.700	0.020	0.028	
b	0.360	0.500	0.014	0.020	
b1	0.380	0.550	0.015	0.022	
С	0.360	0.510	0.014	0.020	
D	4.980	5.280	0.196	0.208	
D1	3.780	4.080	0.149	0.161	
E	3.450	3.750	0.136	0.148	
е	1.270 TYP		0.050 TYP		
e1	3.710	3.910	0.146	0.154	
L	14.900	15.300	0.587	0.602	
θ	45° TYP		45° TYP		

SSIP4 (P/N TMR2505B) package drawing:




SYMBOL	MILLIMETER				
	MIN	NOM	MAX		
A2	0.80	0.90	1.00		
A3	0.55	0.60	0.65		
ь	0.28	50 5050 - 5 05	0.38		
ы	0.27	0.30	0.33		
c	0.20	772—29	0.26		
c1	0.19	0.20	0.21		
D	2.85	2.90	2.95		
E1	2.70	2.80	2.90		
L1	0.20	0.25	0.30		
L2	1.10	1.20	1.30		
L3	11.80	12.00	12.20		
e	1.00BSC				
e1	0.64BSC				

SOT23-5 (P/N TMR2505S) package drawing:



TMR Sensor Position







MultiDimension Technology Co., Ltd.

Address: No.7 Guangdong Road, Zhangjiagang Free Trade Zone, Jiangsu, 215634, China

Web: www.dowaytech.com/en Email: info@dowaytech.com

The information provided herein by MultiDimension Technology Co., Ltd. (hereinafter MultiDimension) is believed to be accurate and reliable. Publication neither conveys nor implies any license under patent or other industrial or intellectual property rights. MultiDimension reserves the right to make changes to product specifications for the purpose of improving product quality, reliability, and functionality. MultiDimension does not assume any liability arising out of the application and use of its products. MultiDimension's customers using or selling this product for use in appliances, devices, or systems where malfunction can reasonably be expected to result in personal injury do so at their own risk and agree to fully indemnify MultiDimension for any damages resulting from such applications.