

AI

E502650

Features

- Glass Passivated Die Construction
- General Purpose 3 Phases Bridge Rectifier Applications
- High Surge Current Capability
- · Lead Free Finish/Rohs Compliant (Note1) ("P"Suffix Designates Compliant. See Ordering Information)
- Epoxy Meets UL 94 V-0 Flammability Rating

Maximum Ratings

- Operating Junction Temperature Range: -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- Maximum Thermal Resistance: 0.88°C/W Junction to Case

Mechanical Data

Mounting Torgue: 2 N·m Maximum


MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
MT5004A	MT5004A	400V	280V	400V
MT5006A	MT5006A	600V	420V	600V
MT5008A	MT5008A	800V	560V	800V
MT5010A	MT5010A	1000V	700V	1000V
MT5012A	MT5012A	1200V	840V	1200V
MT5014A	MT5014A	1400V	980V	1400V
MT5016A	MT5016A	1600V	1120V	1600V

Electrical Characteristics @ 25°C Unless Otherwise Specified

	-		•
Average Forward Current	I _{F(AV)}	50A	T _C = 55°C
Forward Surge Current(Nonrepetitive)	I _{FSM}	500A	60Hz Sine Wave,1cycle,
Peak Forward Voltage	V_{FM}	1.2V	I _{FM} =25A,Pulse measurement, Rating of Per Diode
Peak Reverse Current	I _{RRM}	10µA	Pulse Measurement Rating of Per Diode
Current Squared Time	l²t	1042A ² S	1ms <t<8.3ms rating<br="">of Per Diode</t<8.3ms>
Dielectric Strength	Vdis	2KV	AC 1min, Terminals to Case

Note: 1. High Temperature Solder Exemption Applied, see EU Directive Annex Notes 7a.

50 Amp Three Phases Bridge Rectifier 400 to 1600 Volts



25.00

0.75 0.85

4.90

6.20 6.40

D

Е

F

G

н

0.944 0.029 0.033

0.193

0.244 0.251

TYP.

TYP.





Curve Characteristics





Fig. 3 - Typical Instantaneous Forward Characteristics







Fig. 4 - Typical Reverse Leakage Characteristics





Ordering Information

Device	Packing
Part Number-BP	Bulk: 50PCS/BOX:400PCS/CTN

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. *Micro Commercial Components Corp*. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp*. and all the companies whose products are represented on our website, harmless against all damages. *Micro Commercial Components Corp*. products are sold subject to the general terms and conditions of commercial sale, as published at

https://www.mccsemi.com/Home/TermsAndConditions.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources**. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.