# CTCDRH125F Series From 1.3µH to 1,000µH

# **ENGINEERING KIT #23F**



### **CHARACTERISTICS**

Description: SMD (shielded) power inductor

**Applications:** Power supplies for OA equipment, LCD televisions, PC notebooks, portable communication equipment, DC/DC converters, etc.

Operating Temperature: -40°C to +125°C

Storage Condition: Temperature range = 15°C ~ 28°C;

Humidity = <80% relative humidity Inductance Tolerance: ±20%, ±30%

Testing: Inductance is tested on an HP4284A at 1.0kHz

Packaging: Tape & Reel

Marking: Parts are marked with inductance code

Miscellaneous: RoHS Compliant.

Additional Information: Additional electrical & physical

information available upon request

Samples available. See website for ordering information.

# **SPECIFICATIONS**

Part numbers indicate inductance tolerance available.

M = ±20%, N = ±30%

\*IDC: The DC current at which the inductance decreases to 75% of its nominal value or when  $\Delta T=40^{\circ}C$ , whichever is lower (Ta=20°C).

Part Number	Inductance (µH)	L Test Freq. (KHz)	DCR Max. (Ω)	IDC Max. (A)
CTCDRH125F-1R3N CTCDRH125F-2R1N CTCDRH125F-3R1N CTCDRH125F-4R4N CTCDRH125F-5R8N CTCDRH125F-7R5N CTCDRH125F-7R6N	1.3 2.1 3.1 4.4 5.8 7.5 7.6	1.0 1.0 1.0 1.0 1.0 1.0	.012 .014 .017 .020 .021 .024 .026	8.0 7.0 6.0 5.0 4.4 4.2 4.5
CTCDRH125F-100M CTCDRH125F-120M CTCDRH125F-150M CTCDRH125F-180M CTCDRH125F-220M CTCDRH125F-270M CTCDRH125F-330M CTCDRH125F-330M CTCDRH125F-390M CTCDRH125F-560M CTCDRH125F-560M CTCDRH125F-680M CTCDRH125F-680M CTCDRH125F-680M	10 12 15 18 22 27 33 39 47 56 68	1.0 1.0 1.0 1.0 1.0 1.0 1.0 1.0 1.0 1.0	.03 .03 .03 .03 .04 .05 .06 .07 .08 .11 .12	4.0 3.5 3.3 3.0 2.8 2.3 2.1 2.0 1.8 1.7 1.5
CTCDRH125F-101M CTCDRH125F-151M CTCDRH125F-151M CTCDRH125F-161M CTCDRH125F-221M CTCDRH125F-271M CTCDRH125F-391M CTCDRH125F-391M CTCDRH125F-471M CTCDRH125F-471M CTCDRH125F-681M CTCDRH125F-681M CTCDRH125F-821M CTCDRH125F-821M	100 120 150 180 220 270 330 390 470 560 680 820	1.0 1.0 1.0 1.0 1.0 1.0 1.0 1.0 1.0 1.0	.16 .17 .23 .29 .40 .46 .51 .69 .77 .86 1.2	1.3 1.1 1.0 0.9 0.8 0.8 0.7 0.7 0.6 0.5 0.5
010DhH125F-102M	1000	1.0	1.5	0.4

# **PHYSICAL DIMENSIONS**

Size	A	В	C	D
	Max.	Max.		
mm	12.8	6	7.6±0.2	5±0.2
inches	0.504	0.24	0.30±0.008	0.2±0.007

